



CHB100-110S SERIES

100 WATT 3:1 INPUT

ISOLATED DC-DC CONVERTER

Features

- Efficiency Up to 89%
- Fixed Switching Frequency
- Regulated Outputs
- Remote On/Off
- Low No Load Input Power
- Fully Protected (OTP/OCF/OVP/UVLO)
- 3000Vac I/O Isolation
- Operating Case Temperature -40 to +100°C
- Half Brick Size Meet Industrial Standard
2.28"x2.40"x0.50"
- LVD Approval
- EN 50155 Compliant with External Circuits
- Shock & Vibration EN 50155 (EN 61373) Compliant
- Fire & Smoke EN 45545-2 Compliant
- 3000m Operating Altitude
- Safety Meets IEC/EN/UL 62368-1



MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT		INPUT CURRENT		% EFF. (1)	CAPACITOR LOAD MAX.
			MIN.	MAX.	NO LOAD	FULL LOAD		
CHB100-110S12	66-160 VDC	12 VDC	0 mA	8.3 A	5 mA	1050 mA	86.5	8300μF
CHB100-110S15	66-160 VDC	15 VDC	0 mA	6.7 A	5 mA	1040 mA	87.5	4170μF
CHB100-110S24	66-160 VDC	24 VDC	0 mA	4.17 A	5 mA	1040 mA	87	4170μF
CHB100-110S48	66-160 VDC	48 VDC	0 mA	2.08 A	5 mA	1020 mA	89	1500μF

NOTE:

1. Nominal input voltage 110 VDC.
2. An external input capacitor 47μF for all models are recommended to reduce input ripple voltage.
3. Require a 47μF aluminum capacitor connected between +Vout and -Vout for 48Vout models.
4. To meet en50155 and RIA12 refer to application note.

PART NUMBER

Series	Nominal Input Voltage	Number of Outputs	Nominal Output Voltage	Remote On/Off Logic	Mounting Inserts
CHB100-	II	O	XX	L	-Y (Option)
CHB100	110 : 110 VDC	S : Single	12 : 12VDC 15 : 15VDC 24 : 24VDC 48 : 48VDC	None : Positive	None : M3x0.5 Mounting Inserts -C : Clear Mounting Insert (3.2mm DIA.)

Part Number Example:

CHB100-110S12-C: Half Brick, 100W, 3:1 66-160Vdc Input, Single 12Vdc Output, Positive Logic, Clear Mounting Insert



CHB100-110S Series

TECHNICAL SPECIFICATIONS

(All specifications are typical at nominal input, full load at 25°C unless otherwise noted.)

ABSOLUTE MAXIMUM RATINGS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input Voltage	Continuous	All	-0.3		160	V _{dc}
Input Surge Voltage	100ms max.	All			180	V _{dc}
Operating Case Temperature	At the center part of base plate with derating	All	-40		100	°C
Storage Temperature		All	-55		105	°C

INPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Operating Input Voltage		All	66	110	160	V _{dc}
Input Under Voltage Lockout						
Turn-On Voltage Threshold		All	60	62	64	V _{dc}
Turn-Off Voltage Threshold		All	54	56	58	V _{dc}
Lockout Hysteresis Voltage		All		6		V _{dc}
Maximum Input Current	V _{in} =66V, Full load	All		1.785		A
No-Load Input Current	V _{in} =110V, I _o =0A	See Model Number Table				mA
Input Filter	Pi filter	All				
Inrush Current (I ² t)	As per ETS300 132-2	All			0.1	A ² s
Input Reflected Ripple Current	P-P thru 12uH inductor, 5Hz to 20MHz	All		50		mA

OUTPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Voltage Set Point Accuracy	V _{in} =110V, Full load, T _c =25°C	All	-1.0		+1.0	%
Output Voltage Regulation						
Load Regulation	Full load to no load	All			±0.2	%
Line Regulation	V _{in} =High line to low line, full load	All			±0.2	%
Temperature Coefficient	T _c =-40°C to 100°C	All			±0.03	%/°C
Output Voltage Ripple and Noise (5Hz to 20MHz bandwidth)						
Peak-to-Peak	Full load, 10uF aluminum solid capacitor (for 48Vout 47uF Aluminum capacitor)and 1uF ceramic capacitors	12Vo			150	mV
		15Vo			150	
		24Vo			240	
		48Vo			480	
RMS.		5Vo			60	mV
		12Vo			60	
		24Vo			100	
		48Vo			200	
Output Current Range	V _{in} = 66 to 160V	See Model Number Table				A
Over Current Protection	Hiccup mode. Auto recovery	All	110	130	160	%
Short Circuit Protection		All	Continuous, Auto Recovery			
External Load Capacitance	Full load (resistive)	See Model Number Table				uF
Output Voltage Trim Range	P _o ≤ max. rated power, I _o ≤ I _{o_max} .	All	-10		+10	%
Output Voltage Remote Sense Range	P _o ≤ max. rated power, I _o ≤ I _{o_max} . % of nominal V _o	All			+10	%
Over Voltage Protection	Limited voltage, % of nominal V _o	All	115	125	140	%

EFFICIENCY

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
100% Load	V _{in} =110V	See Model Number Table				%



CHB100-110S Series

DYNAMIC CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Output Voltage Current Transient						
Error Band	25% step load change d _i /d _t =0.1A/us (within 1% V _{out} nominal)	All	±10			%
Recovery Time			500			us
Turn-On Delay and Rise Time	Full load (constant resistive load)					
Turn-On Delay Time, From On/Off Control	V _{on/off} to 10%V _{o_set} , Remote on	All	10			ms
Turn-On Delay Time, From Input	V _{in_min.} to 10%V _{o_set} , Power up	All	25			ms
Output Voltage Rise Time	10%V _{o_set} to 90%V _{o_set}	All	15			ms

ISOLATION CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Isolation Voltage (100% factory Hi-Pot tested @2sec.)	1 Minute; input to output	All	3000			V_{ac}
	1 Minute; input to case (base plate)		1500			V_{ac}
	1 Minute; output to case (base plate)		500			V_{ac}
Isolation Resistance	Input to output	All	1000			MΩ
Isolation Capacitance	Input to output	All	500			pF

FEATURE CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Switching Frequency	Pulse width modulation (PWM), fixed	All	225	250	275	KHz
On/Off Control, Positive Remote On/Off Logic, Refer to -Vin Pin						
Logic Low (Module Off)	V _{on/off} at I _{on/off} =1.0mA	All	0		1.8	V
Logic High (Module On)	V _{on/off} at I _{on/off} =0.0uA, Pin open=on	All	Open Circuit			V
On/Off Current (for Both Remote On/Off Logic)	I _{on/off} at V _{on/off} =0V	All	0.3			1 mA
Leakage Current (for Both Remote On/Off Logic)	Logic high, V _{on/off} =15V	All	30			uA
Off Converter Input Current	Shutdown input idle current	All	1.5			5 mA
Over Temperature Shutdown	Temperature at the center part of base plate, non-latching	All	105			°C
Over Temperature Recovery			90			

GENERAL SPECIFICATIONS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
MTBF	I _o =100% of I _{o_max.} ; MIL-HDBK - 217F_Notice 1, GB, 25°C	All	830			K hours
Weight		All	95			grams
Case Material	Plastic, DAP, UL 94V-0					
Base plate Material	Aluminum					
Potting Material	UL 94V-0					
Pin Material	Base: Copper Plating: Nickel with Matte Tin					
Shock/Vibration	MIL-STD-810F/EN 61373 Compliant					
Humidity	95% RH max. Non Condensing					
Altitude	3000m Operating Altitude, 12000m Transport Altitude					
Thermal Shock	MIL-STD-810F					
Fire & Smoke	EN 45545-2 Compliant					



CHB100-110S Series

EMC SPECIFICATIONS (External components required, please refer to application note.)

EMI	Meets EN 55011 (with external filter) Meets EN 55032 (with external filter) EN 50155 Compliant (with external filter)	Class A Class B
ESD	EN 61000-4-2 Contact $\pm 6\text{kV}$ EN 61000-4-2 Air $\pm 8\text{kV}$	Perf. Criteria A Perf. Criteria A
Radiated Immunity	EN 61000-4-3 10V/m	Perf. Criteria A
Fast Transient	EN 61000-4-4 $\pm 2\text{ kV}$, external components required	Perf. Criteria A
Surge	EN 61000-4-5 $\pm 1\text{kV}$, external components required	Perf. Criteria A
Conducted immunity	EN 61000-4-6 10Vr.m.s	Perf. Criteria A
Interruptions of Voltage Supply	EN 50155 Class S3: 20ms with external hold up circuit	Perf. Criteria A
Supply Change Over	EN 50155 Class C2: 30ms with external hold up circuit	Perf. Criteria B
Application Note Link CHB100-110S Series App Notes		
Packaging Information Link Packaging Information		

Immunity to Environmental Conditions

Phenomenon	EN50155; 2017 Reference Clause(s)	Reference Standard	Test Conditions	Result
Low Temperature Start-up test	13.4.4	EN 60068-2-1	Class OT4 Temperature: -40°C Duration: 2 hrs	Pass
Dry Heat Test	13.4.5	EN 60068-2-2	Class OT4 Temperature: 70°C Dry heat thermal test Cycle A	Pass
Low Temperature Storage Test	13.4.6	EN 60068-2-1	Temperature: -40°C Duration: 16 hrs	Pass
Cyclic Damp Heat Test	13.4.7	EN 60068-2-30	Temperature: 55°C and -55°C Humidity: 90~96% RH Duration: 48 hrs	Pass
Random Vibration Test	13.4.11	EN 61373	Temperature: $25^{\circ}\text{C} \pm 10^{\circ}\text{C}$ Humidity: 50% $\pm 25\%$ RH Frequency range: 5 ~ 150 Hz X axis: 0.44 m/s^2 Y axis: 0.69 m/s^2 Z axis: 0.98 m/s^2 Duration: 10 min / axis	Pass
Simulated Long Life Test at Increased Random Vibration Levels	13.4.11	EN 61373	Temperature: $25^{\circ}\text{C} \pm 10^{\circ}\text{C}$ Humidity: 50% $\pm 25\%$ RH Frequency range: 5 ~ 150 Hz X axis: 2.5 m/s^2 Y axis: 3.96 m/s^2 Z axis: 5.72 m/s^2 Duration: 5 hrs / axis	Pass
Shock Test	13.4.11	EN 61373	Temperature: $25^{\circ}\text{C} \pm 10^{\circ}\text{C}$ Humidity: 50% $\pm 25\%$ RH a. Test Condition 1 ($\pm X$ axes) Units are non-operating. Pulse shape: Half-sine waveform Impact acceleration: 50 m/s ² Pulse duration: 30 ms Number of shocks / Orientation: 6 shocks (3 shocks for $\pm X$ axis) b. Test Condition 2 ($\pm Y$ and $\pm Z$ axes) Units are non-operating. Pulse shape: Half-sine waveform Impact acceleration: 30 m/s ² Pulse duration: 30 ms Number of shocks: 12 shocks (3 shocks for each $\pm$ axis) Orientation: $\pm Y$ and $\pm Z$ axes	Pass



CHB100-110S Series


EN45545-2 Fire & Smoke Test Conditions

Item		Standard	Hazard Level
R22	Oxygen Index Test	EN 45545-2: 2013 EN ISO 4589-2: 2006	HL1, HL2, HL3
	Smoke Density Test	EN 45545-2: 2013 EN ISO 5659-2: 2013	HL1, HL2, HL3
	Smoke Toxicity Test	EN 45545-2: 2013 NF X70-100: 2006	HL1, HL2, HL3
R23	Oxygen Index Test	EN 45545-2: 2013 EN ISO 4589-2: 2006	HL1, HL2, HL3
	Smoke Density Test	EN 45545-2: 2013 EN ISO 5659-2: 2013	HL1, HL2, HL3
	Smoke Toxicity Test	EN 45545-2: 2013 NF X70-100: 2006	HL1, HL2, HL3
R24	Oxygen Index Test	EN 45545-2: 2013 EN ISO 4589-2	HL1, HL2, HL3
R25	Glow - Wire Test	EN 45545-2:2013 EN 60695-2-11:2001	HL1, HL2, HL3
R26	Vertical Flame Test	EN 45545-2: 2013 EN 60695-11-10: 2013	HL1, HL2, HL3


CHARACTERISTIC CURVE

Power Derating Curve


CHB100-110S12,15,24 Derating Curve
without Heatsink (Vin=110V)




CHB100-110S48 Derating Curve
without Heatsink (Vin=110V)



CHB100-110S12,15,24 Derating Curve
with Heatsink HBT127 (Vin=110V)




CHB100-110S48 Derating Curve
with Heatsink HBT127 (Vin=110V)






CHB100-110S Series


CHB100-110S12,15,24 Derating Curve with Heatsink HBL210 (Vin=110V)




CHB100-110S48 Derating Curve with Heatsink HBL210 (Vin=110V)



CHB100-110S12,15,24 Derating Curve with Heatsink HBT254 (Vin=110V)




CHB100-110S48 Derating Curve with Heatsink HBT254 (Vin=110V)




Performance Data


CHB100-110S12
Eff Vs Io @25 Deg. C




CHB100-110S12
Pd Vs Po @25 Deg. C



CHB100-110S15
Eff Vs Io @25 Deg. C




CHB100-110S15
Pd Vs Po @25 Deg. C






CHB100-110S Series


CHB100-110S24
Eff Vs Io @25 Deg. C




CHB100-110S24
Pd Vs Po @25 Deg. C



CHB100-110S48
Eff Vs Io @25 Deg. C



CHB100-110S48
Pd Vs Po @25 Deg. C





CHB100-110S Series


MECHANICAL SPECIFICATION

CASE HB

All Dimensions In Inches(mm)

Tolerances Inches: X.XX= ± 0.02 , X.XXX= ± 0.010

Millimeters: X.X= ± 0.5 , X.XX= ± 0.25



CINCON Electronics Co. Ltd.
Add: 14F, No. 306, Sec.4, Hsin Yi Rd., Taipei, Taiwan
Tel: 886-2-27086210
Fax: 886-2-27029852
E-mail: sales@cincon.com.tw
Web: www.cincon.com