

# AI 0,5-8 WH-B 3000 - Ferrule

3240663

<https://www.phoenixcontact.com/us/products/3240663>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: white



## Your advantages

- The sleeves are supplied on large reels, containing a quantity of up to 3000 each
- Ferrules in tape format for automatic processing

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3240663       |
| Packing unit                         | 3,000 pc      |
| Minimum order quantity               | 3,000 pc      |
| Sales key                            | BH34          |
| Product key                          | BH3414        |
| GTIN                                 | 4046356625777 |
| Weight per piece (including packing) | 0.115 g       |
| Weight per piece (excluding packing) | 0.093 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | DE            |

# AI 0,5-8 WH-B 3000 - Ferrule



3240663

<https://www.phoenixcontact.com/us/products/3240663>

## Technical data

### Product properties


|                    |                                                   |
|--------------------|---------------------------------------------------|
| Product type       | Cable end sleeve                                  |
| Conductor category | stranded conductors, class 2, 5, 6 / B, C, K, M   |
| Product property   | Taped design for automated production             |
|                    | UL certified                                      |
|                    | Made from tin-plated electrolytic copper          |
|                    | Design in accordance with DIN 46228-1 and UL 486F |
|                    | With "Easy Entry" (conical insertion area)        |
|                    | Plastic collar made of polypropylene              |
|                    | Halogen-free                                      |
|                    | Long/short-term temperature: +105°C/+120°C        |

### Connection data

#### Conductor connection

|                                       |         |
|---------------------------------------|---------|
| Conductor cross section flexible max. | 0.5 mm² |
| Conductor cross section AWG max.      | 20      |
| Stripping length                      | 11 mm   |

### Dimensions

|                                           |                                                                                      |
|-------------------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing                       |  |
| Sleeve length                             | 14 mm                                                                                |
| Length contact range                      | 8 mm                                                                                 |
| Maximum stripping length                  | 11 mm                                                                                |
| Ferrule diameter                          | 1.1 mm                                                                               |
| Sleeve wall thickness                     | 0.15 mm                                                                              |
| Insulating collar thickness               | 0.25 mm                                                                              |
| Inner dimensions of the insulating collar | 2.5 mm                                                                               |

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | white (RAL 9010)               |
| Material                               | CU-DHP                         |
| Flammability rating according to UL 94 | HB                             |
| Coating                                | galvanically tin-plated        |
| Surface characteristics                | Tin-plated                     |
| Components                             | free from silicone and halogen |

### Mechanical properties

# AI 0,5-8 WH-B 3000 - Ferrule



3240663

<https://www.phoenixcontact.com/us/products/3240663>

## Technical data

|               |       |
|---------------|-------|
| Sleeve length | 14 mm |
|---------------|-------|

## Environmental and real-life conditions

### Ambient conditions

|                        |                                             |
|------------------------|---------------------------------------------|
| Permanent temperature  | 105 °C (-40 °C no load / 0 °C dynamic load) |
| Short-term temperature | 120 °C                                      |

## Standards and regulations

|                              |                        |
|------------------------------|------------------------|
| Design according to standard | DIN 46228-4, UL 486F-E |
|------------------------------|------------------------|

## Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

# AI 0,5-8 WH-B 3000 - Ferrule

3240663

<https://www.phoenixcontact.com/us/products/3240663>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240663>



**cULus Listed**

Approval ID: E488001

# AI 0,5-8 WH-B 3000 - Ferrule



3240663

<https://www.phoenixcontact.com/us/products/3240663>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400201 |
| ECLASS-15.0 | 27400201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000005 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27121700 |
|-------------|----------|

# AI 0,5-8 WH-B 3000 - Ferrule



3240663

<https://www.phoenixcontact.com/us/products/3240663>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)