




LOADING PATTERN MATING SIDE

f	K	K	K	K	K	K	K	6	6	6	K	K	K	K	K	K	K
e	5	F	F	F	F	F	F	F	K	5	5	5	5	5	5	5	5
d	5	F	F	F	F	F	F	F	K	5	5	5	5	5	5	5	5
c	5	F	F	F	F	F	F	F	K	6	6	6	6	6	6	6	6
b	5	F	F	F	F	F	F	F	K	5	5	5	5	5	5	5	5
a	5	F	F	F	F	F	F	F	K	5	5	5	5	5	5	5	5
z	K	K	K	K	K	K	K	6	6	6	K	K	K	K	K	K	K
POS	01									10						15	
																	19

LOADED CONNECTOR ASSEMBLY
(FOR EXAMPLE)






SEATING PLANE
FOR CONNECTOR



HM2P71PNW2P5 **LEAD FREE INDICATOR : LF = LEAD FREE (DIGIT 15 & 16)**
PLATING CODE (DIGIT 13 AND 14)
(REF DRW NO. BS,C , 201844 , 003)

NOTES

- THIS PRODUCT IS CSA APPROVED.
 - THIS PRODUCT IS UL RECOGNIZED.
 - MEASURED AT THE BOTTOM.
 - MATERIAL CONTACT: PHOSPHORBRONZE
HOUSING: CREAM WHITE GLASS FILLED POLYESTER UL-94V0
 - CONNECTOR PRINTED WITH P/N AND DATE CODE.
 - FOR ACTUAL CONTACT LOADINGS, SEE LOADING PATTERN MATING SIDE.
 - SHAPE OF CONNECTOR HOUSING CAN ALTER DEPENDING ON PRODUCTION LOCATION
 - THE PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING : BS, A , 201572 , 001
- CATALOG NO: HM2P71PNW2P5----

mat'l. code SEE NOTE 4				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MILLIPACS											
ltr	ecn no		dr	date		tolerances unless otherwise specified						title									
A	I03-0043		MKV	2003/08/18		angles linear		.0±0.2				MPACS 5+2R STR HDR PF CONN TYPE B 19 POS.									
B	I05-0171		MINI	2005/10/03				.00±0.1													
C	I06-0077		MINI	2006/06/23				0°±1°													
				dr	MINI K VANDANATH		2003/08/18				dwg no				sheet 1 of 1				size		
				engr	BIJU K PAUL		2003/08/18				BS, C ,203028, 070								A3		
				chr	BIJU K PAUL		2006/06/23														
				appd	BIJU K PAUL		2006/06/23														
sheet index		revision		C																	
		sheet		1																	