


SKINDICHT® SHV-M

SKINDICHT® SHV-M, robust special sealing cable gland, watertight with high strain relief, gentle cable clamping



Optimum strain relief



Robust



Waterproof

Benefits

- Watertight
- Gentle cable clamping
- Robust
- High strain relief

Application range

- Watertight cable gland with conical sealing element.
- Pumps
- Floater switches

Product Make-up

- Metric connection thread acc. to DIN EN 60423
- Basis for technical information DIN IEC 62444

Note

- Counter nut to be used: SKINDICHT® SM-M
- Suitable accessory: SKINDICHT® SHV sealing cones
- Example description:
SHV-M 20/11/7
20 = metric connection thread
11 = PG function thread

Last Update (04.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® SHV-M

7 = clear opening of sealing cone

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class-Description: Cable screw gland

Caution:

The installation dimensions
can be found in appendix T21

Material:

Body: nickel-plated brass

Sealing cone: CR

O-ring: NBR

Protection rating:

IP 68 - 10 bar

Temperature range:

-20°C to +80°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® SHV-M

Article number	Article designation / size	Clamping range ØF mm	Function thread PG	SW1/SW2 mm	Overall length C mm	Thread length D mm	Clear opening seal	Pieces / PU
SKINDICHT® SHV-M								
52105270	M 12 x 1,5	3 - 4.8	7	14.0 / 14.0	26.0	5	5.0	50
52105280	M 16 x 1,5	4.5 - 5.8	9	18.0 / 17.0	26.5	5	6.0	50
52105290	M 16 x 1,5	5.5 - 6.8	9	18.0 / 17.0	26.5	5	7.0	50
52105300	M 20 x 1,5	6 - 6.8	11	22.0 / 20.0	31.0	6	7.0	25
52105310	M 20 x 1,5	6.5 - 8.8	11	22.0 / 20.0	31.0	6	9.0	25
52105320	M 20 x 1,5	6.5 - 8.8	13.5	22.0 / 22.0	32.5	6	9.0	25
52105330	M 20 x 1,5	9 - 10.8	13.5	22.0 / 22.0	32.5	6	11.0	25
52105340	M 20 x 1,5	9 - 10.8	16	24.0 / 24.0	34.5	6	11.0	25
52105350	M 20 x 1,5	9.5 - 12.8	16	24.0 / 24.0	34.5	6	13.0	25
52105360	M 20 x 1,5	13 - 14.8	16	24.0 / 24.0	34.5	6	15.0	25
52105370	M 25 x 1,5	13.5 - 15.8	21	30.0 / 30.0	38.5	7	16.0	25
52105380	M 25 x 1,5	15 - 17.8	21	30.0 / 30.0	38.5	7	18.0	25
52105390	M 25 x 1,5	17.5 - 19.8	21	30.0 / 30.0	38.5	7	20.0	25
52105400	M 32 x 1,5	17.5 - 21.8	29	40.0 / 40.0	42.5	8	22.0	10
52105410	M 32 x 1,5	19 - 23.8	29	40.0 / 40.0	42.5	8	24.0	10
52105420	M 32 x 1,5	23 - 25.8	29	40.0 / 40.0	42.5	8	26.0	10

Last Update (04.09.2020)
 ©2020 Lapp Group - Technical changes reserved
 Product Management www.lappkabel.de
 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03.16