
Part Number : 2067600001
Product Description : 698MHz-2.7GHz Cellular Ceramic Antenna, Low-profile, SMT
Series Number : 206760
Status : Active
Product Category : Antennas
Engineering Part Number : 20676-0001



Documents and Resources

Drawings

2067600001_sd.pdf

2067600001-PK.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2067600001-AS.pdf

2067600001-PS.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Antennas
Series	206760
Description	698MHz-2.7GHz Cellular Ceramic Antenna, Low-profile, SMT
Component Type	Surface Mount Device Antenna
Function	Signal
Product Name	Full LTE SMT Antenna
Protocol	Cellular
Type	Cellular Antenna, Internal, LPWAN
UPC	191128861250

Electrical

Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	698
Band#2 F_End (MHz)	2700
Band#2 F_Start (MHz)	1710
Electrical Connectivity	SMD
Peak Gain (dBi)	1.3 @ 698 MHz, 4.4 @ 1710 MHz
Return Loss - S11 (dB)	< -5
Total Efficiency	>60% @ 698 MHz, >70% @ 1710 MHz

Physical

Downloaded from Arrow.com.

Cable Length	N/A
Length	38.00mm
Mounting Style	Surface Mount
Net Weight	3.436/g
Packaging Type	Embossed Tape on Reel
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	3.00mm
Width	8.00mm

Downloaded from Arrow.com.