

Especificaciones

La foto es representativa

Eaton 20FE

NOT STAND-SPECIAL ORDER

General specifications

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	20FE
UPC	051712832380
EAN	5027590467827
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	90 mm
PRODUCT WIDTH	150 mm
PRODUCT WEIGHT	39.5 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC Designed and tested to BS88 part 4 IEC 60269-4

Especificaciones del producto

AMPERAGE RATING	20 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	500 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	62 mm
MOUNTING DIMENSION	M6
CURRENT TYPE	AC/DC
CLASS	Class aR
FUSE SHAPE	Offset bolted tags
COLOR	None
INTERRUPT RATING	200 kA RMS Sym, 50 kA at 500 Vdc
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	FE
SUITABLE FOR	EC-600 Trip indicator kit (indicator + clips) TI700 Fuse indicator MAI Microswitch/adaptor MBI Microswitch/adaptor
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

Recursos

DECLARATIONS OF CONFORMITY

[eaton-high-speed-british-standard-fuse-declaration-of-conformity-eu250044en.pdf](#)

[eaton-high-speed-british-standard-fuse-declaration-of-conformity-uk250922en.pdf](#)

MCAD MODEL

[eaton-hs-bs88-body-fuses-mcad-3d-models-15-100a-fe.stp](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

FECHA:



Eaton Corporation plc
Eaton House
Carretera 30 Pembroke
Dublín 4, Irlanda
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. Todos los derechos reservados.