


1. MATERIALS AND FINISHES:
SMA STR BHD JACK - BRASS, GOLD PLATING

AMC RA PLUG:
HOUSING - PBT, BLACK
CONTACT & GROUND CONTACT - PHOSPHOR BRONZE, GOLD PLATING

CABLE - 1.13 MM CABLE
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
3. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 95-902-545-XXX AND DATE CODE"

SCALE 1.000



☒ FREQUENCY: DC - 6 GHz	☒ CONTINUITY
☐ VSWR: ____ MAX.	☒ HI-POT: 200 VRMS
☐ INS. LOSS: ____ dB MAX.	☐ OTHER:

NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE METRIC [INCHES] AND TOLERANCES ARE: $<0.5\text{mm} = \pm 0.05\text{mm}$ [$<0.020 = \pm 0.002$] $>0.5 - 6\text{mm} = \pm 0.1\text{mm}$ [$>0.020 - 0.236 = \pm 0.004$] $>6.00 - 30\text{mm} = \pm 0.2\text{mm}$ [$>0.236 - 1.181 = \pm 0.008$] $>30.00 - 120\text{mm} = \pm 0.3\text{mm}$ [$>1.181 - 4.725 = \pm 0.012$] ANGLES = $\pm 1^\circ$			MATERIAL SEE NOTES		TITLE SMA STR BHD JACK FRONT MOUNT IP 67 TO AMC RA PLUG USING 1.13 MM CABLE VARIOUS LENGTH		Amphenol RF		
THIRD ANGLE PROJ. 			REFERENCE		EAR# 10473		SIZE B		DRAWING NO. 95-902-545-XXX		REV	
									ITEM NO. 95-902-545-XXX		[	
									PART NO. 95-902-545-XXX		]	