

SMD Schottky Barrier Rectifiers

CDBB220-G Thru. CDBB2100-G

Reverse Voltage: 20 to 100 Volts

Forward Current: 2.0 Amp

RoHS Device




Features

- Ideal for surface mount applications.
- Easy pick and place.
- Plastic package has Underwriters Lab. flammability classification 94V-0.
- Built-in strain relief.
- Low forward voltage drop.

Mechanical data

- Case: JEDEC DO-214AA, molded plastic.
- Terminals: solderable per MIL-STD-750, method 2026.
- Polarity: Color band denotes cathode end.
- Approx. weight: 0.093 grams



Maximum Ratings and Electrical Characteristics

Parameter	Symbol	CDBB 220-G	CDBB 240-G	CDBB 260-G	CDBB 280-G	CDBB 2100-G	Units
Max. repetitive peak reverse voltage	V _{RRM}	20	40	60	80	100	V
Max. DC blocking voltage	V _{DC}	20	40	60	80	100	V
Max. RMS voltage	V _{RMS}	14	28	42	56	70	V
Peak surge forward current, 8.3ms single half sine-wave superimposed on rate load (JEDEC method)	I _{FSM}	50					A
Max. average forward current	I _O	2.0					A
Max. instantaneous forward voltage at 2.0A	V _F	0.50		0.70	0.85		V
Max. DC reverse current at T _A =25°C rated DC blocking voltage T _A =100°C	I _R	0.5 10					mA
Max. thermal resistance (Note 1)	R _{θJA} R _{θJL}	75 17					°C/W
Max. operating junction temperature	T _J	125					°C
Storage temperature	T _{STG}	-65 to +150					°C

Notes: 1. Thermal resistance from junction to ambient and junction to lead mounted on P.C.B. with 0.2×0.2 inch² copper pad area.

RATING AND CHARACTERISTIC CURVES (CDBB220-G thru CDBB2100-G)

Fig.1 Reverse Characteristics




Fig.2 Forward Characteristics




Fig.3 Junction Capacitance




Fig.4 Current Derating Curve




Fig.5 Non-repetitive Forward Surge Current

