





PRODUCT NUMBER
SEE TABLE, SHEET 2






spec ref				dr		Chen-Hong Tan		2006/08/17		projection		MM		size		A3		scale		2:1					
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Terry Luo		2019/04/24						ecn no		ELX-DG-33324-1									
ASME Y14.5				chr		-		-						rel level		Released									
-				appr		Heaven Cen		2019/04/25		product family		AirMax Accessories													
surface		3.2		linear		0.X		±0.3		Amphenol FCI		title		7.2mm R/A GUIDE BLADE		dwg no		10045588		rev		C			
		0.XX																						±0.10	
		0.XXX																						±0.050	
ASME Y14.5		angular		0°		±2°				cat. no.		-		Product - Customer Drw						sheet 1 of 2					

Product number
10045588-101LF

NOTES:

- 1. MATERIAL: ZINC ALLOY.
- 2. FINISH: ZINC YELLOW CHROMATE.
- 3. APPLICATION SPECIFICATION: GS-20-045.
- 4. REFER TO CUSTOMER DRAWING 10035911 FOR INFORMATION REGARDING PCB LAYOUT OF POWER AND GUIDE MODULES RELATIVE TO SIGNAL MODULES.
- 5. RIGHT ANGLE PIN MODULE HAS THE SAME PCB FOOTPRINT AS RIGHT ANGLE RECEPTACLE MODULE (REF P/N 10045367 SHEET 2).
- 6. THIS PRODUCT MEETS EUROPEAN DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
- 7. PACKAGING MEETS GS-14-920 LEAD FREE LABELING SPECIFICATION.



spec ref				dr	Chen-Hong Tan	2006/08/17	projection 	MM 	size	A3	scale	1:1	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Terry Luo	2019/04/24			ecn no				ELX-DG-33324-1
ASME Y14.5				chr	-	-			rel level				Released
-				appr	Heaven Cen	2019/04/25	product family		AirMax Accessories				
surface 3.2  ASME Y14.5	linear	0.X	±0.3	Amphenol FCi	title	7.2mm R/A GUIDE BLADE 2/3 PAIR			dwg no	10045588		rev	
		0.XX	±0.10									C	
		0.XXX	±0.050										
	angular	0°	±2°		cat. no.	-	Product - Customer Drw			sheet 2 of 2			