

**Part Number :** [1203410075](#)

**Product Description :** Micro-Change (M12) CAT6A Front Panel-Mount Receptacle, 8 Poles, X-Coded, Female (Straight), 0.0185m (.728") Length

**Series Number :** 120341

**Status :** Obsolete

**Product Category :** Circular Industrial Connectors

**Engineering Part Number :** ER2D2U303



---

## Documents and Resources

### Drawings

[1203410075 sd.pdf](#)

[PK-120341-075-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

Status	Obsolete
Category	Circular Industrial Connectors
Series	120341
Description	Micro-Change (M12) CAT6A Front Panel-Mount Receptacle, 8 Poles, X-Coded, Female (Straight), 0.0185m (.728") Length
IP Rating	IP67
Performance Category	6A
Product Name	Micro-Change (M12) Cat6A
Type	PCB Mount
UPC	884982163355

### Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	48V

### Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	X-Coded
Length	0.0185m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M12 x 1.0
Net Weight	9.391/g
Orientation	Straight
Panel Mount	Front
Poles	8
Temperature Range - Operating	-40° to +70°C

Wire/Cable Type	N/A
Wire Size (AWG)	N/A

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Micro-Change M12 CAT6A Cordsets and Receptacles	<u>120341</u>

---

This document was generated on May 27, 2026

Obsolete