




LOC		DIST		REVISIONS								
-		-										
P		LTR		DESCRIPTION			DATE		DWN		APVD	
		B		REV PER ECO 14-012149			8-12-14		CT		DH	



- 1 HOUSING: LCP, UL94V0, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE.
POST: BRASS WIRE
- 2 PAD CONTACT AREA: 1.27µm MIN GOLD
SHALLOW EYE CONTACT AREA: 0.76µm MIN GOLD
PCB TAILS CONTACT: 1.27µm MIN TIN-LEAD (93/7) OVER
1.27µm MIN NICKEL OVER ALL
POST: 1.27µm MIN NICKEL PLATED
- 3 PLATED THROUGH HOLE PER 114-13056, FIGURE 4
- 4 SEE TABLE 1 FOR INTERCONNECTIONS TO
BACKPLANE CONNECTOR.
- 5 PAD CONTACT AREA: 1.27µm MIN GOLD
SHALLOW EYE CONTACT AREA: 0.76µm MIN GOLD
PCB TAILS CONTACT: 1.27µm MIN MATTE TIN
OVER 1.27µm MIN NICKEL OVER ALL
POST: 1.27µm MIN NICKEL PLATED
- 6 PAD CONTACT AREA: 1.27µm MIN GOLD
SHALLOW EYE CONTACT AREA: 0.76µm MIN GOLD
PCB TAILS CONTACT: 1.27µm MIN TIN-LEAD (60/40) OVER
1.27µm MIN NICKEL OVER ALL
POST: 1.27µm MIN NICKEL PLATED

TYPICAL INTERCONNECTION
FOR EACH COLUMN
(WAFER):
1, 2, 3, 4, 5, 6, 7, 8,
9, 10, 11, 12, 13, 14, 15 & 16

CONTACT USAGE	DAUGHTERCARD CONNECTOR PIN	BACKPLANE CONNECTOR PIN
POWER	ax, bx, cx	ax, bx, cx, dx
POWER	ex, fx, gx	fx, gx, hx, ix
Not Connect	dx	ex



6	2286663-3
5	2286663-2
2	2286663-1
PLATING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 6-10-14	NAME RIGHT-ANGLE PLUG ASSEMBLY, 7 ROW, CENTER, 20.3mm, MULTIGIG RT 2-R, DAUGHTERCARD CONNECTOR, POWER	
DIMENSIONS: mm		CHK D. HOANG 6-10-14	PRODUCT SPEC 108-2072	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. HOANG 6-10-14	APPLICATION SPEC 114-13056	
0 PLC ±.5 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±1°		SIZE 114-13056	RESTRICTED TO A100779C=2286663	
MATERIAL SEE TABLE		WEIGHT 10.33g	Customer Drawing	
SCALE 6:1		SHEET 1	OF 1	
REV B				