



Part Number : [357460410](#)

Product Description : VersaBlade Female Crimp Terminal, 24 AWG, Type A

Series Number : 35746

Status : Active

Product Category : Crimp Terminals



Documents and Resources

Drawings

[357460410_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[351500000AS_ENG-000.pdf](#)

[351500000AS_KOR-000.pdf](#)

[351800400-001.pdf](#)


[351800600-001.pdf](#)

Tooling Specifications

[CS-35745-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	35746
Description	VersaBlade Female Crimp Terminal, 24 AWG, Type A
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	756054339107

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.253/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.45mm max.
Wire Size (AWG)	24

Wire Size mm ²	0.29
---------------------------	------

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Natural	<u>351500300</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Blue	<u>351500304</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Natural, Glow-Wire Capable	<u>351500309</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Natural	<u>351500310</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Blue	<u>351500314</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Natural, Glow-Wire Capable	<u>351500319</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural	<u>351500400</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Blue	<u>351500404</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	<u>351500409</u>
VersaBlade Hybrid Receptacle	<u>351500410</u>

Housing, with Mounting Ears, 4 Circuits, Natural	
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Red	<u>351500412</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Blue	<u>351500414</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	<u>351500419</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Natural	<u>351500600</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Blue	<u>351500604</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Natural, Glow-Wire Capable	<u>351500609</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Natural	<u>351500610</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Red	<u>351500612</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Blue	<u>351500614</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Natural, Glow-Wire Capable	<u>351500619</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Yellow, Glow-Wire Capable	<u>351503309</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Yellow, Glow-Wire	<u>351503319</u>

Capable	
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Yellow, Glow-Wire Capable	<u>351503419</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Yellow, Glow-Wire Capable	<u>351503609</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Yellow, Glow-Wire Capable	<u>351503619</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Blue, Glow-Wire Capable	<u>351504319</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Blue, Glow-Wire Capable	<u>351504419</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Blue, Glow-Wire Capable	<u>351504619</u>
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, 9 Circuits, Full Flange Panel Mount, Natural, Glow-Wire Capable	<u>2026500909</u>
VersaBlade Multi-Module 2-2 Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	<u>2041020429</u>
VersaBlade Multi-Module 4-2 Hybrid Receptacle Housing, 6 Circuits, Natural, Glow-Wire Capable	<u>2041020609</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Natural, Glow-Wire Capable	<u>2041020209</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>2041020219</u>
VersaBlade Multi-Module Hybrid Plug Housing, 4 Circuits, Friction	<u>2041020409</u>

Lock, Natural, Glow-Wire Capable	
VersaBlade Multi-Module Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>2041020419</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type A, Natural	<u>351810200</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Natural	<u>359650200</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Blue	<u>359650204</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Natural	<u>359650210</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Blue	<u>359650214</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Natural, Glow-Wire Capable	<u>359659200</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type A, Yellow, Glow-Wire Capable	<u>359659203</u>
VersaBlade Hybrid Plug Housings	<u>35151</u>
VersaBlade Multi-Module Hybrid Receptacle Housings	<u>35180</u>
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housings	<u>35524</u>

Application Tooling

Global

Description	Part Number
Extraction and Activation Tool	<u>638132700</u>
Hand Crimp Tool for Industry	<u>638196900</u>

Standard 1.78mm Tab Terminals, 26-24 AWG Wire	
FineAdjust Applicator for .070 Male and Female Crimp Terminals, 24 AWG	<u>639044200</u>

This document was generated on Apr 15, 2026