



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : CDAE-026-046

REV.: 1


PART NO. : A264B/UBW/C430/R/F14-13

ECN :

Page:

1/6

■ Package Dimensionas:



■ Notes:

- 1.All dimensions are in millimeters, tolerance is 0.25mm except being specified
- 2.Lead spacing is measured where the lead emerge from the package

LED PART NO.	Chip		Lens Color
	Material	Emitted Color	
264-10UBW/C430	GaN/SiC	Blue	White Diffused

Office : 7C Building, Lian Hua Port Industrial District, Lian Hua Shan

Bonded Pricessing Zone Pan Yu, Guang Zhou, China

TEL. : (020)84860913,84860914

FAX : (020)84860600

http : //www.everlight.com

T019275,B90560780



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : CDAE-026-046 REV.: 1

PART NO. : A264B/UBW/C430/R/F14-13 ECN : Page: 2/6

■ Descriptions:

- 1.ARRAY=Plastic Holder+Combinations of Lamp
- 2.The array will easily mount the applicable lamps on any panel up to

■ Features:


- 1.Low power consumption
- 2.High efficiency and low cost
- 3.Good control and free combinations on the colors of LED lamps
- 5.Good lock and easy to assembly
- 6.Stackable and easy to assembly
- 7.Stackable vertically and easy to assembly
- 8.Versatile mounting on P.C board or panel
- 9.Stackable horizontally and easy to assembly

■ Applications:

- 1.Used as indicators of indicating the Degree, Functions, Positions etc, in electronic instruments.



■ LED LAMP ARRAYS SELECTION GUIDE:





EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : CDAE-026-046 REV.: 1

PART NO.: A264B/UBW/C430/R/F14-13 ECN : Page: 4/6

■ Absolute Maximum Ratings at Ta = 25°C

Parameter	Symbol	Rating	Unit
Forward Current	IF	30	mA
Operating Temperature	Topr	-40 to +85	°C
Storage Temperature	Tstg	-40 to +100	°C
Soldering Temperature	Tsol	260 ± 5	°C
Electrostatic Discharge	ESD	1000	V
Power Dissipation	Pd	140	mW
Peak Forward Current(Duty 1/10 @ 1KHz)	IF(Peak)	70	mA
Reverse Voltage	VR	5	V

■ Electronic Optical Characteristics :

Parameter	Symbol	Min.	Typ.	Max	Unit	Condition
Luminous Intensity	Iv	63.00	120.00	/	mcd	IF= 20 mA
Viewing Angle	2θ 1/2	/	45	/	deg	IF= 20 mA
Peak Wavelength	λ p	/	428	/	nm	IF= 20 mA
Dominant Wavelength	λ d	/	466	/	nm	IF= 20 mA
Spectrum Radiation Bandwidth	△ λ	/	65	/	nm	IF= 20 mA
Forward Voltage	VF	/	3.8	4.5	V	IF= 20 mA
Reverse Current	IR	/	/	50	μ A	VR= 5 V









EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : CDAE-026-046 REV.: 1

PART NO. : A264B/UBW/C430/R/F14-1 ECN : Page: 5/6

■ Typical Electro-Optical Characteristic Curves:

(UB)





EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : CDAE-026-046 REV.: 1

PART NO. : A264B/UBW/C430/R/F14-13 ECN : Page: 6/6

■ Reliability test items and conditions

NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 PCS	0/1
2	Temperature Cycle	H : +85°C 30min § 5 min L : -55°C 30min	50 CYCLES	76 PCS	0/1
3	Thermal Shock	H : +100°C 5min § 10 sec L : -10°C 5min	50 CYCLES	76 PCS	0/1
4	High Temperature Storage	TEMP : 100°C	1000 HRS	76 PCS	0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 PCS	0/1
6	DC Operating Life	TEMP : 25°C IF = 20 mA	1000 HRS	76 PCS	0/1
7	High Temperature / High Humidity	85°C /85% RH	1000 HRS	76 PCS	0/1