

Products

Documentation

Resources

My Account

Customer Support

5554901

- 1

Product Details

Live Product Chat

US Only

8:30am - 5pm ET, Mon - Fri



5554901

- 1

Active

2.16 [.085] Printed Circuit Board Connectors

Always EU RoHS/ELV Compliant

(

Statement of Compliance

)

Product Highlights:

- ? Receptacle
- ? Number of Positions = 50
- ? PCB Mount Style = Right Angle
- ? Standard Orientation
- ? Standard Profile

View all Features

 |

Find Similar Products

Quick Links

- Check Pricing & Availability

Search for Tooling

Product Feature Selector

Contact Us About This Product

Documentation & Additional Information	
Product Drawings: ? RECEPTACLE ASSEMBLY, SHIELED, 50 POSITION, BAIL LOC... (PDF, English) Catalog Pages/Data Sheets: ? None Available Product Specifications: ? None Available Application Specifications: ? None Available Instruction Sheets: ? None Available CAD Files: (CAD Format & Compression Information) ? 2D Drawing (DXF, Version O) ? 3D Model (IGES, Version O) ? 3D Model (STEP, Version O) List all Documents	Additional Information: ? Product Line Information Related Products: ? Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? Gender = Receptacle ? Number of Positions = 50 ? PCB Mount Style = Right Angle ? Orientation = Standard ? Profile = Standard ? Shielded = Yes ? Mating Connector Lock = With ? Mating Connector Lock Type = Bail Lock ? PCB Retention Feature = No ? Grounded = Yes ? Panel Thickness (mm [in]) = 1.57 [0.062] ? Color = Black ? Shield Material = Die Cast Metal ? Screw Size = 4 -40 Mechanical Attachment: ? Panel Attachment = With ? Panel Attachment Style = Rear Mount ? Plate Material = Thermoplastic ? Comb Material = Thermoplastic ? Bail -Clip Material = Stainless Steel ? Bail -Clip Finish = Passivated ? Ground Bracket Material = Carbon Steel	Termination Related Features: ? Solder Tail Contact Plating = Tin Body Related Features: ? Shield Plating = Bright Nickel over Copper ? Ground Bracket Plating = Zinc Contact Related Features: ? Contact Mating Area Plating Material = Gold over Nickel ? Contact Material = Copper Alloy Housing Related Features: ? Housing Material = Thermoplastic Industry Standards: ? RoHS/ELV Compliance = RoHS compliant, ELV compliant ? Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C ? RoHS/ELV Compliance History = Always was RoHS compliant Operation/Application: ? Application = SCSI Other: ? Brand = AMP