



Part Number : [1200868496](#)
Product Description : Nano-Change (M8)
Single-Ended Cordset, 3 Poles, A-Coded, Male
(Straight) to Pigtail, 0.25mm² Black PUR LSOH
Cable, 1.0m (3.28') Length
Series Number : 120086
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : 403006H08M010




Documents & Resources

Drawings
[1200868496_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120086
Description	Nano-Change (M8) Single-Ended Cordset, 3 Poles, A-Coded, Male (Straight) to Pigtail, 0.25mm ² Black PUR LSOH Cable, 1.0m (3.28') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Protocol	N/A
Type	Single Ended
UPC	78172538144

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	4.10mm (.161")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass

Material - Plating Mating	Gold
Net Weight	32.200/g
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	24

This document was generated on Apr 22, 2025
