



[+](#) CIRCUIT PROTECTION

VERY FAST-ACTING CHIP



✓ Active

TE CONNECTIVITY (TE) 1206SFV15.0FM/032-2

Fuse | 1206

1206SFV15.0FM/032-2
TE Internal Number: RF4327-000

Always EU RoHS/ELV Compliant

- Current Rating (A) **15**
- Interrupt Voltage (Max) (VDC) **32**
- Cold DCR (Nominal) (Ω) **.0035**
- I^2t (A²sec)² (Nominal) (Ω) **24.5**
- Interrupt Current (VDC) **50A @ 32**

Product Specifications

Product Specification

[1206SFV Family \(Marked\)](#)
PDF
English



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Form Factor (inch)	1206
	Product Type	Fuse
	Fuse Type	DC Very Fast Acting Chip Fuse
	Form Factor (mm)	3216
Electrical Characteristics	Current Rating (A)	15
	Interrupt Voltage (Max) (VDC)	32
	Cold DCR (Nominal) (Ω)	.0035
	I^2t (A ² sec) ² (Nominal) (Ω)	24.5
	Interrupt Current (VDC)	50A @ 32
	Breaking Capacity (VDC)	50A @ 32
	Clear Time (Min) (100% Rated Current) (Hr)	4
Termination Features	Construction	Surface Mount

Usage Conditions	Operating Temperature (Max) (°C)	125
Industry Standards	UL File Number	E197536
Product Compliance	Statement of Compliance PDF VIEW ALL PRODUCT COMPLIANCE	