

20A, 45V - 200V Schottky Barrier Surface Mount Rectifier

FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- Guard ring for overvoltage protection
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21


APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- DC to DC converters


MECHANICAL DATA

- Case: TO-263AB (D²PAK)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 1A whisker test
- Polarity: As marked
- Weight: 1.37g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I_F	20	A
V_{RRM}	45 - 200	V
I_{FSM}	150	A
$T_{J\ MAX}$	150	°C
Package	TO-263AB (D ² PAK)	
Configuration	Dual dies	



TO-263AB (D²PAK)



ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)							
PARAMETER	SYMBOL	MBRS 2045 CT-Y	MBRS 2060 CT-Y	MBRS 20100 CT-Y	MBRS 20150 CT-Y	MBRS 20200 CT-Y	UNIT
Marking code on the device		MBRS 2045CT	MBRS 2060CT	MBRS 20100CT	MBRS 20150CT	MBRS 20200CT	
Repetitive peak reverse voltage	V _{RRM}	45	60	100	150	200	V
Reverse voltage, total rms value	V _{R(RMS)}	31	42	70	105	140	V
Forward current	I _F	20					A
Surge peak forward current, 8.3ms single half sine wave superimposed on rated load	I _{FSM}	150					A
Peak repetitive reverse surge current ⁽¹⁾	I _{RRM}	1	0.5				A
Peak repetitive forward current (Rated V _R , Square wave, 20KHz)	I _{FRM}	20					A
Critical rate of rise of off-state voltage	dv/dt	10,000					V/μs
Junction temperature	T _J	-55 to +150					°C
Storage temperature	T _{STG}	-55 to +150					°C

Notes:

1. $t_p = 2.0\mu\text{s}$, 1.0KHz

THERMAL PERFORMANCE

PARAMETER		SYMBOL	TYP	UNIT
Junction-to-case thermal resistance	MBRS2045CT-Y MBES2060CT-Y	$R_{\theta JC}$	1.5	°C/W
Junction-to-case thermal resistance	MBRS20100CT-Y MBES20150CT-Y MBES20200CT-Y	$R_{\theta JC}$	2	°C/W

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT	
Forward voltage per diode ⁽¹⁾	MBRS2045CT-Y	I _F = 10A, T _J = 25°C	V _F	-	0.70	V	
	MBRS2060CT-Y			-	0.80	V	
	MBRS20100CT-Y			-	0.85	V	
	MBRS20150CT-Y MBRS20200CT-Y			-	0.99	V	
	MBRS2045CT-Y	I _F = 10A, T _J = 125°C		-	0.60	V	
	MBRS2060CT-Y			-	0.70	V	
	MBRS20100CT-Y			-	0.75	V	
	MBRS20150CT-Y MBRS20200CT-Y			-	0.87	V	
Reverse current @ rated V _R per diode ⁽²⁾	MBRS2045CT-Y MBRS2060CT-Y MBRS20100CT-Y MBRS20150CT-Y MBRS20200CT-Y	T _J = 25°C	I _R	-	100	μA	
	MBRS2045CT-Y	T _J = 125°C		-	15	mA	
	MBRS2060CT-Y			-	10	mA	
	MBRS20100CT-Y MBRS20150CT-Y MBRS20200CT-Y			-	5	mA	

Notes:

1. Pulse test with $PW = 0.3\text{ms}$
2. Pulse test with $PW = 30\text{ms}$

ORDERING INFORMATION

ORDERING CODE ⁽¹⁾	PACKAGE	PACKING
MBRS20xCT-Y	TO-263AB (D ² PAK)	800 / Tape & Reel

Notes:

1. "x" defines voltage from 45V(MBRS2045CT-Y) to 200V(MBRS20200CT-Y)

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics






Fig.5 Maximum Non-Repetitive Forward Surge Current



CHARACTERISTICS CURVES


($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.6 Typical Transient Thermal Impedance




PACKAGE OUTLINE DIMENSIONS

TO-263AB (D²PAK)



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	4.44	4.70	0.175	0.185
A2	2.03	2.79	0.080	0.110
b	0.68	0.94	0.027	0.037
c	0.36	0.53	0.014	0.021
c2	1.14	1.40	0.045	0.055
D	8.25	9.25	0.325	0.364
E	-	10.50	-	0.413
e	2.41	2.67	0.095	0.105
H	14.60	15.88	0.575	0.625
L	2.29	2.79	0.090	0.110
L3	1.14	1.40	0.045	0.055

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	10.80	0.425
B	8.30	0.327
C	1.27	0.050
D	4.05	0.159
E	15.95	0.628
F	2.54	0.100
G	9.775	0.385

MARKING DIAGRAM



P/N = Marking Code
 G = Green Compound
 YWW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.