




**Part Number :** [5016461200](#)  
**Product Description :** 2.00mm Pitch, iGrid  
Receptacle Crimp Housing, Dual Row, Positive  
Lock, 12 Circuits, Natural  
**Series Number :** 501646  
**Status :** Active  
**Product Category :** Connector Housings



## Documents & Resources

### Drawings

[5016461200\\_sd.pdf](#)

### 3D Models and Design Files

[5016461200.dxf](#)

[5016461200.pdf](#)

[5016461200\\_stp.zip](#)

### Specifications

[5016460000-A00.pdf](#)

[5016460000-A01.pdf](#)

[5016469200-200.pdf](#)

[5016460000-PS-000.pdf](#)

[5016461000-PS-000.pdf](#)

[5016461001-PS-001.pdf](#)

[PS-501646-001-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS

- REACH SVHC

- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	501646
Description	2.00mm Pitch, iGrid Receptacle Crimp Housing, Dual Row, Positive Lock, 12 Circuits, Natural
Application	Signal, Wire-to-Board
Product Name	iGrid
UPC	822350087148

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	12
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Number of Rows	2

Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
iGrid Vertical, Dual Row, Through Hole Headers	<u>501645</u>
iGrid Vertical, Dual Row, Through Hole Headers	<u>503091</u>
iGrid Right-Angle, Dual Row, Through Hole Headers	<u>501876</u>
iGrid Right-Angle, Dual Row, Through Hole Headers	<u>208659</u>

### Use with Part(s)

Description	Part Number
iGrid Female Crimp Terminals	<u>501647</u>
iGrid Female Crimp Terminals	<u>501648</u>
iGrid Female Crimp Terminals	<u>503095</u>

---

This document was generated on Mar 21, 2025