



E32-TC200 2M

Fiber optic sensor head, through-beam, M4 cylindrical axial, R25 fiber, 2 m cable

Specifications

Sensing method	Through-beam
Shape	Threaded
Size	M4
Application	Object detection
Temperature range	-40-70 °C
Sensing distance	2300 mm
Cable length	2 m
Bending radius	25 mm
Free cut	✓
Material core	Plastic
Degree of protection (IP)	IP67
Sensing surface orientation	Top-view
Material sheath	Polyethylene

Accessories



E39-F1

Long-distance lens unit for E32 through-beam fibers with M2.6 thread



E39-F2

Focal lens, side view unit for E32 through-beam optical fibers

Related products



E3X-ZV and E3X-MZV

Smart Fiber Amplifier



E3NX-CA

High-performance color
mark sensor



E3NX-CA

High-performance color
mark sensor



E3NX-MA

Smart Fiber Amplifier Units



E3NX-FA

High-performance digital
fiber amplifier



E3X-NA

Digital fiber amplifier with
potentiometer adjustment

Downloads

CAD Library



EAC Mark removal Discontinuation Notice

EN PDF 221 KB



Fiber Optic Sensors Group Catalogue

EN PDF 7.54 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 26 June, 2025. Click here for [terms of use](#).

OMRON

INDUSTRIAL AUTOMATION | [INDUSTRIAL.OMRON.EU](https://industrial.omron.eu)