



**Part Number :** [1300310041](#)

**Product Description :** DeviceNet Mini-Change Receptacle, 5 Poles, Male (Straight) with DeviceNet Thin Trunk Cable, 1/2 - 14 NPT Threads, 4.0m (13.12') Length

**Series Number :** 130031

**Status :** Active

**Product Category :** Circular Industrial Connectors

**Engineering Part Number :** DND5100-M040



---

## Documents and Resources


### Drawings

[1300310041\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Connectors
Series	130031
Description	DeviceNet Mini-Change Receptacle, 5 Poles, Male (Straight) with DeviceNet Thin Trunk Cable, 1/2 - 14 NPT Threads, 4.0m (13.12') Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	DeviceNet Trunk,Mini-Change
Type	Single Ended (pigtail)
UPC	78678803033

### Agency

CSA	LR6837
-----	--------

### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	300V AC/DC

### Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single

Length	4.0m
Material - Component	Nickel-plated Zinc Die-Cast
Mounting Thread Size	1/2" - 14 NPT
Net Weight	565.000/g
Orientation	Straight
Panel Mount	Front
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Thin Standard Cable
Wire Size (AWG)	22

---

This document was generated on May 22, 2026