

Part Number : 2153482112
Product Description : Pre-Crimped Lead Squba 3.6 Male-to-Pigtail, Tin (Sn) Plating, 150.00mm Length, 18 AWG, Red
Series Number : 215348
Status : Active
Product Category : Power and Signal Cable Assemblies

Documents and Resources

Drawings

2153482112_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	215348
Description	Pre-Crimped Lead Squba 3.6 Male-to-Pigtail, Tin (Sn) Plating, 150.00mm Length, 18 AWG, Red
Application	Power, Signal, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Squba 3.6 Terminal-to Pigtail
Keyword	Squba 3.6
Product Name	Squba
UPC	195842350021

Electrical

Current - Maximum per Contact	11.5A
Voltage - Maximum	600V

Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Red
Gender	Male-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Resin	Modified Polystyrene
Net Weight	1.689/g
Number of Rows	1

Downloaded from Arrow.com.

Packaging Type	Bag
Pitch - Mating Interface	3.60mm
Plating min - Mating	2.540µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Size (AWG)	18

Downloaded from Arrow.com.