

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	14MAR'07	SC	JK
	B	REVISED PER ECR-09-011788	25MAY'09	SC	JK
	C	REVISED PER ECR-19-009721	01JUL2019	M.G	D.Z
	C1	ECR-25-247422	25JUN2025	KD	D,Z




(FIG 1.)RECOMMENDED PANEL OPENING
5 DIMENSIONS: TOLERANCE±0.15




1 THIS HOUSING ACCEPTS TAB TERMINAL:
-TAB CONTACT: 177917-□ (AWG#16-#20)
177916-□ (AWG#22-#26)
2 MATING CONN. P/N
-PLUG HSG: 368576-□
-REC CONTACT: 177915-□ (AWG#16-#20)
177914-□ (AWG#22-#26)
3 APPLICABLE DOUBLE LOCK PLATE: 177919-1
* IT SHOULD BE USED CERTAINLY WHEN CABLE ASS'Y
4 GENERAL TOLERANCES:±0.3
5 APPLICABLE PANEL THICKNESS: 0.8~2.0 (SEE FIG.1)
6 INSERT CONN. FROM PRESS DIRECTION SIDE FOR METAL PANEL.
7 EDGE OF THICKNESS MAY MUST DOT ROUND FOR MOLDED PANEL.
8 MATERIAL: PA66,UL94V-0
COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT)





SECTION X-X



COLOR	PART NUMBER
BLUE	368588-6
YELLOW	368588-4
NATURAL	368588-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL 8

FINISH -

DWN SC KIM
CHK BW KANG
APVD JK SONG
PRODUCT SPEC 108-5410
APPLICATION SPEC 114-5175
WEIGHT -

TE Connectivity

NAME PDL 6P CAP HSG 3.96mm D/R P/M (GWT)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-368588	-

CUSTOMER DRAWING | SCALE 3:1 | SHEET 1 OF 1 | REV C1

1470-19 (3/13)

Downloaded from Arrow.com.