
DWG NO.	SH	CUSTOMER	CUSTOMER P/N	CUST. REV
1-0133	1			


DASH #	MODEL #	IMPEDANCE Ω
-1	BJ28	50
-2	UBJ28	75


DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO EMERSON CONNECTIVITY SOLUTIONS AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION

REVISIONS

REV	DESCRIPTIONS	DATE	APPROVED
U	ECO 53008	1-26-11	T. KOHLER







RECOMMENDED PANEL CUTOUT
SCALE 1:1

3. SOCKET CONTACT COAXIAL BNC TYPE INSULATED FEED THRU BULKHEAD JACK, 50 AND 75 OHM VERSIONS

2. MAX PANEL THK .156

1. FINISH: NICKEL

NOTES: UNLESS OTHERWISE SPECIFIED.

N/A	
BLANK LENGTH (REF. ONLY)	
N/A	
SURFACE AREA	

INTERPRET DRAWING PER MIL-STD-100. DIMENSIONS ARE IN INCHES AND INCLUDE FINISH THICKNESS UNLESS OTHERWISE SPECIFIED.

TOL: UNLESS SPECIFIED.
.XX ±
.XXX ± .005
.XXXX ±
ANGLE ±
CRITICAL

DRN	B. RYAN 4-18-11
CHK	T. KOHLER 4-19-11
QUALITY	
MANUF	
APPROVED	
PRO/E FILE NO.	1-0133

MATERIAL:

FINISH:

DO NOT SCALE DWG

cinch CONNECTIVITY SOLUTIONS a belgroup
Cinch Connectivity Solutions
299 Johnson Ave. Ste. 100
Waseca, MN 56093
1-800-247-8256

TITLE:

BJ28/UBJ28

SIZE	CAGE CODE	DRAWING NO.	REV.
A	14949	1-0133	U

SCALE	DATE	SHEET
3/1	9-15-66	1 OF 2

Downloaded from Arrow.com.
Please read our datasheet & drawing disclaimer here.