

NOTES:


1. MATERIALS AND FINISHES:
N STR PLUG IP 67 - BRASS, NICKEL PLATING
CABLE - LMR 400
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM

3. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 95-909-173-XXX AND DATE CODE"

THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	12-Feb-19	10464	VR
B	NO CHANGE TO THIS SHEET	20-Mar-19	10943	PL
D	NO CHANGE TO THIS SHEET	09-Apr-19	11201	SK
D	ADDED 95-909-173-300	24-FEB-25	17372	LP



LENGTH TABLE		
PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH 'L' IN INCHES [METERS]
95-909-173-006	-	6.00 [0.152]
-	95-909-173M025	9.84 [0.250]
95-909-173-012	-	12.00 [0.305]
95-909-173-018	-	18.00 [0.457]
-	95-909-173M050	19.69 [0.500]
95-909-173-024	-	24.00 [0.610]
-	95-909-173M075	29.53 [0.750]
95-909-173-036	-	36.00 [0.914]
-	95-909-173M100	39.37 [1.000]
95-909-173-048	-	48.00 [1.219]
-	95-909-173M150	59.06 [1.500]
95-909-173-072	-	72.00 [1.829]
-	95-909-173M200	78.74 [2.000]
95-909-173-096	-	96.00 [2.438]
95-909-173-108	-	108.00 [2.743]
-	95-909-173M300	118.11 [3.000]
95-909-173-120	-	120.00 [3.048]
-	95-909-173M400	157.48 [4.000]
95-909-173-240	-	240.00 [6.096]
95-909-173-300	-	300.00 [7.620]
95-909-173-360	-	360.00 [9.144]
-	95-909-173M10L	393.70 [10.000]
95-909-173L050	-	600.00 [15.240]
-	95-909-173M20L	787.40 [20.000]
95-909-173L075	-	900.00 [22.860]
-	95-909-173M30L	1181.10 [30.000]
95-909-173L100	-	1200.00 [30.480]

DESIGN REQUIREMENTS:

- ☒ FREQUENCY DC - 6 GHz
- ☒ CONTINUITY
- ☐ VSWR: ---- : 1 MAX.
- ☒ HI-POT: 750 VRMS
- ☐ INS. LOSS: ---- dB MIN.
- ☐ OTHER

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:
2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES
±.015 (0.381 mm) ±.005 (0.127 mm) ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

SEE NOTES

REFERENCE

EAR # 8886

CONFIGURATION LEVEL: In Work

FINISH

DRAWN

VIJAY N M

ENGINEER

VIJAY N M

APPROVED

K.CAPOZZI

CAD FILE

DATE

29-Jan-19

DATE

29-Jan-19

DATE

09-Apr-19

TITLE

N STR PLUG IP 67 TO
N STR PLUG IP 67
USING LMR 400 CABLE
VARIOUS LENGTH

SCALE: 1.0:1.0

DWG SIZE

B

REV

D

TOLERANCE TABLE

LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

Amphenol RF

www.amphenolrf.com

DRAWING NO.95-909-173-XXX

ITEM NO.95-909-173-XXX

PART NO.95-909-173-XXX