Part Number : 2132740001
Product Description : PowerPlane BusBar Assembly, Middle Size, Vertical Mount, Single Hole, Open Side Walls, Siver (Ag) Plated
Series Number : 213274
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2132740001_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2132740001-AS-000.pdf

2132740001-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	213274
Description	PowerPlane BusBar Assembly, Middle Size, Vertical Mount, Single Hole, Open Side Walls, Siver (Ag) Plated
Component Type	PCB Receptacle
Product Name	PowerPlane
UPC	195842626768

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	200.0A
Voltage - Maximum	1000V

Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Durability (mating cycles max)	200

Downloaded from Arrow.com.

First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	10.028/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Screw

Downloaded from Arrow.com.