

Current refinements (click  to remove) Search Tips

 Region  USA  Product Family  HSTTA Heat Shrink  Text Search: 'HSTTA50-48-5'

Your search criteria matched only one product, shown below.



Dual Wall Polyolefin DAMPSHRINK™ Heat Shrink Tubing in 4 ft Pieces

- For damp locations
- Flexible tubing with an adhesive inner wall which seals and protects components from moisture and corrosion
- The 3:1 shrink ratio is a benefit when working with connector -to-cable transitions
- Material Type: Polyolefin CrossLinked with adhesive
- Shrink Ratio: 3:1
- Temperature Range:-67°F to 230°F (55°C to 110°C)
- Flammability: Outer wall flame retardant
- Voltage Rating: 600V
- Mil Spec: AMSDTL-23053/4 Class 3

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| Part Number:                            | HSTTA50-48-5                                                                        |
| RoHS Compliancy Status:                 | Compliant                                                                           |
| Part Description:                       | Dual Wall Adhesive Lined Thin Wall Heat Shrink                                      |
| Material:                               | Polyolefin cross-linked with adhesive.                                              |
| Color:                                  | Black                                                                               |
| Military Specification:                 | AMS-DTL-23053/4 Class 3                                                             |
| Length (ft.):                           | 4                                                                                   |
| Flammability Rating:                    | Outer Wall Flame Retardant                                                          |
| Max. Recovered I.D. (In.):              | .160                                                                                |
| Max. Recovered I.D. (mm):               | 4.1                                                                                 |
| Min. Expanded I.D. (In.):               | .500                                                                                |
| Min. Expanded I.D. (mm):                | 12.7                                                                                |
| Nominal Diameter (In.):                 | 1/2                                                                                 |
| Nominal Diameter (mm):                  | 12.7                                                                                |
| Nominal Recovered Wall Thickness (In.): | .070                                                                                |
| Nominal Recovered Wall Thickness (mm):  | 1.8                                                                                 |
| Shrink Ratio:                           | 3:1                                                                                 |
| Temperature Range:                      | -67°F to 230°F(55°C to 110°C)                                                       |
| Min. Order UOM:                         | PC                                                                                  |
| Min. Order Qty.:                        | 5                                                                                   |
| BOM Qty. (# of Pkgs.)                   | <input type="text" value="0"/>                                                      |
| Add to My Catalog                       |  |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.