


1734383-1 Product Details

Have a Question?

Chat with a Product Information Specialist



1734383-1

TE Internal Number: 1734383-1

Active

View 3D PDF

Universal Serial Bus (USB) Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Size = Standard
- A Series
- Receptacle
- Without Locking Feature
- 4 Ports

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings: - RECEPTACLE ASS'Y, FOURFOLD STACKED, THRU-HOLE, RIGHT... (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: (CAD Format & Compression Information) 2D Drawing (DXF, Version D) 3D Model (IGES, Version D) 3D Model (STEP, Version D) List all Documents	Additional Information: - Product Line Information Related Products: - Tooling
---	--

Product Features (Please use the Product Drawing for all design activity)

Product Type Features: - Size = Standard - Gender = Receptacle - Number of Ports = 4 - Orientation = Right Angle - Comment = Quadruple Stacked Mechanical Attachment: - Mount Location = Top Electrical Characteristics: - Panel Ground Type = Ground Finger Termination Related Features: - Termination Method = Solder - Tail Length (mm [in]) = 2.36 [0.093] Body Related Features: - Series = A - Locking Feature = Without - LED = Without - Panel Ground = With - PCB Mount Retention Type = Kinked Leg, Straight Leg - Shell Plating = Nickel over Copper - Assembly Process Feature = Without Pick and Place Cover - Locating Post(s) = Without - Number of Positions = 16	Contact Related Features: - Contact Termination Type = Through Hole - Contact Plating, Mating Area, Material = Gold - Contact Plating, Mating Area, Thickness = 15 Microinches Housing Related Features: - Housing Color = Black Industry Standards: - RoHS/ELV Compliance = RoHS compliant, ELV compliant - Lead Free Solder Processes = Reflow solder capable to 245°C, Reflow solder capable to 260°C - RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: - Applies To = Printed Circuit Board - PCB Thickness, Recommended (mm [in]) = 1.60 [0.063] Packaging Related Features: - Panel Ground Location = Center - Packaging Method = Tray Other: - Brand = AMP
---	---

BOOKMARK

Corporate Information

Who We Are
Investors
News Room
Supplier Portal
Careers

Quick Links

Check Distributor Inventory
Cross Reference
Find Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat with Us
Find a Phone Number
Search Knowledge Base
Manage Your Account

Sign up for our eNewsletter

Enter your email address



Follow us on:

