

M8-PCB-THT-2PC-4P-DCOD-F-ANG-SHLD



Image is for illustration purposes only. Please refer to product description.

Part number	21 42 000 0019
Specification	M8-PCB-THT-2PC-4P-DCOD-F-ANG-SHLD
HARTING eCatalogue	https://harting.com/2142000019

Identification

Category	Connectors
Series	Circular connectors M8
Element	PCB connector
Specification	Angled for rear mounting
Description of hood/housing	11 mm

Version

Termination method	Wave soldering termination
Gender	Female
Shielding	Shielded
Number of contacts	4
Coding	D-coding

Technical characteristics

Rated current	4 A
Rated voltage	60 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$



Pushing Performance
Since 1945

Technical characteristics

Tightening torque	1 Nm Lock nut
Limiting temperature	-40 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP67

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-2-114
----------------	-----------------

Commercial data

Packaging size	1
Net weight	29 g
Country of origin	Czechia
European customs tariff number	85366990
GTIN	5713140225015
eCl@ss	27460201 PCB connector (board connector)
ETIM	EC002637



Pushing Performance
Since 1945

Commercial data

UNSPSC 24.0

39121415
