

Product data sheet

Specifications



Power Cord Kit (6 EA), Locking, C19 TO C20, 1.2M (4FT), Red

AP8714SX340

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or component type	Power cord
Input Connection Type	IEC 60320 C20
Cable length	1.21 m
Number of cables	6

Physical

Colour	Red
Height	300 mm
Width	70 mm
Depth	70 mm
Net weight	1.64 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Max line current	16 A
Input current limits	16 A

Output

Max current draw	16 A
Number of power socket outlets	1 IEC 60320 C19
Power cable length	1.2 m

Conformance

Product certifications	CCC CSA PSE UL listed VDE
------------------------	---------------------------------------

Environmental

Ambient air temperature for operation	0...75 °C
---------------------------------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Relative humidity	20...80 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...75 °C
Storage Relative Humidity	20...80 %
Storage altitude	0...15240 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	30 cm
Package 1 Width	7 cm
Package 1 Length	7 cm
Package 1 Weight	1.64 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
REACH Regulation	REACH Declaration
Halogen-free status	Product contains halogen above thresholds

Energy efficiency	
Energy Efficiency Optimized	Energy efficient product

Use Again

Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

