





PRODUCT NO.
10099439-002LF
10099439-003C-TRLF
10099439-004C-TRLF



spec ref				dr	Louis Ng	2010/05/01	projection 	MM 	size	A3	scale	2.000
tolerance std ASME Y14.5	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Jeffrey Lim	2016/09/22			ecn no	ELX-S-24900-1		
				chr	-	-			rel level			Released
				appr		Koon-Poh Tay			2016/10/06	product family		
surface 	linear	0.X	±0.25	Amphenol FCi	title SAS PLUG R/A TYPE ASSY, Z-HT. 0.20				dwg no	10099439		rev G
		0.XX	±0.15									
		0.XXX	±0.050									
	angular	0°	±2°	cat. no.		Product - Customer Drw				sheet 1 of 3		

1.23 $\pm$ 0.05(22X)

A

C

SECTION J-J
SCALE 5.000

CONTACT SURFACE FLUSH
TO DATUM A $\pm$ 0.03

0.08 $\pm$ 0.05

A

C






SECTION K-K
SCALE 5.000

(1.00)
(APPLY TO ALL
SOLDERTAILS)

C


5.58 $\pm$ 0.20
(APPLY TO ALL
SOLDERTAILS)

SECTION J-J
SCALE 3.000





10099439-002 WITH PICK-UP CAP ATTACHED

10099439-003 WITH PICK-UP CAP ATTACHED

spec ref				dr	Louis Ng	2010/05/01	projection  MM 	size	A3	scale	2.000
tolerance std ASME Y14.5	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Jeffrey Lim	2016/09/22		ecn no	ELX-S-24900-1		
				chr	-	-					
				appr	Koon-Poh Tay	2016/10/06					product family
surface 	linear	0.X	±0.25	Amphenol FCI	title SAS PLUG R/A TYPE ASSY, Z-HT. 0.20			dwg no 10099439	rev G		
		0.XX	±0.15								
		0.XXX	±0.050								
	angular	0°	±2°								

PRODUCT NO.
SEE TABLE



NOTES:

- MATERIAL:
HOUSING & CAP: HIGH TEMPERATURE THERMOPLASTIC, BLACK, UL94V-0
 ADHESIVE TAPE: POLYIMIDE
CONTACT & HOLD DOWN: COPPER ALLOY
- FINISH:
CONTACT: 1.27um MIN. Ni UNDERPLATE OVERALL,
1.91um MIN. 100% MATTE Sn(LEAD-FREE) ON SOLDER TAIL,
0.76um MIN. Au ON CONTACT AREA
HOLD DOWN: 1.91um MIN. 100% MATTE Sn(LEAD-FREE) OVER
1.27um MIN. Ni UNDERPLATE OVERALL
- RECOMMENDED PCB THICKNESS: 1.00mm
- PRODUCT SPECIFICATION: GS-12-282
- PACKAGING SPECIFICATION: GS-14-952(TRAY); GS-14-1038(TAPE & REEL)
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-47-0004
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE
REFLOW OVEN
- A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH
HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION

spec ref				dr	Louis Ng	2010/05/01	projection MM	size	A3	scale	1.000
tolerance std ASME Y14.5	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Jeffrey Lim	2016/09/22		ecn no ELX-S-24900-1			
				chr	-	-		rel level Released			
				appr	Koon-Poh Tay	2016/10/06		product family			
surface ✓	linear	0.X	±0.25	Amphenol FCi	title SAS PLUG R/A			dwg no	10099439		rev G
		0.XX	±0.15								
		0.XXX	±0.050		TYPE ASSY, Z-HT. 0.20						
	angular	0°	±2°		cat. no.	Product - Customer Drw				sheet 3 of 3	