



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	POWER								SIGNAL							
		E2	P8	P7	P6	P5	P4	P3	P2	P1	6	5	4	3	2	1	E1
51915-126-- NOTE 3	D C B A		PE	PE	PE	PE	PF	PF	PF	PF	S	S	S	S	S	S	
			P	P	P	P	P	P	P	P	R	R	R	R	R	R	
			N	N	N	N	N	N	N	N	N	N	N	N	N	N	



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
S	[N/A]	SIGNAL
R	[N/A]	SIGNAL
P	[N/A]	SIGNAL
N	[N/A]	SIGNAL
PF	[2.34]	POWER
PE	[1.07]	POWER

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ± 0.3	COPY		www.fciconnect.com	
A	DG07-0120	JMG	03/30/07	angles	0.XX ± 0.13	projection		title 24S + 8P R/A PRESS-FIT RECEPTACLE	
					0.XXX ± 0.051			product family PwrBlade code 213	
				dr	0° ± 2°			size dwg no 51915-126 sheet 1 of 4	
				enrg	JM GUO 03/30/07				
				chr	RYAN YUAN 03/30/07				
				appd	GARY HSIEH 03/30/07				
					JOSEPH HSIA 03/30/07				
sheet index	revision sheet	A	A	A	A	scale 1:1			
		1	2	3	4				

Pro/E


cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.





All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NUMBER
51915-126--
NOTE 3



BROKEN-OUT SECTION A-A
SCALE 2:1



BROKEN-OUT SECTION B-B
SCALE 2:1



PARTIAL SECTION E-E

mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ± 0.3	COPY		www.fciconnect.com	
A					0.XX ± 0.13	projection		title	
				angles	0.XXX ± 0.051	MIM		24S + 8P	
				dr	0° ± 2°	scale		R/A PRESS-FIT RECEPTACLE	
				enr	JM GUO 03/30/07	product family		PwrBlade	code
				chr	RYAN YUAN 03/30/07	size		dwg no	213
				appd	GARY HSIEH 03/30/07	A		51915-126	sheet
					JOSEPH HSIA 03/30/07	1:1			2 of 4
sheet index	revision sheet								

cage code 22526

Pro/E

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

4

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51915-126-- NOTE 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

2. HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
3. PLATING:
51915-126, 51915-126LF PLATING SPEC. WAS SHOWN IN THE PRINT OF 10064183.
4. MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.
5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.
6. PACKAGED IN TRAYS.

PCB NOTES:

7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
8. MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.
9. $\varnothing 1.151 \pm 0.025$ DRILLED HOLES PLATED WITH
0.008 MIN SnPb OR Sn OVER 0.03
TO 0.08 Cu PLATING TO ACHIEVE
 $\varnothing 1.02 \pm 0.07$ HOLE.
10. "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
11. CONNECTOR KEEP-OUT ZONE.
12. USE FCI CAM TOOL 430140-XXX
TO APPLY CONNECTOR TO PCB.

mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com		
ltr	ecn no.	dr	date	linear	0.X ±0.3		COPY		projection	title		24S + 8P R/A PRESS-FIT RECEPTACLE		
A					0.XX ±0.13									
					0.XXX ±0.051									
				angles	0° ±2°					product family		PwrBlade		code
				dr	JM GUO	03/30/07	MM					size	dwg no	213
				enrg	RYAN YUAN	03/30/07	scale					A	51915-126	sheet
				chr	GARY HSIEH	03/30/07							4 of 4	
				appd	JOSEPH HSIA	03/30/07								
sheet index		revision sheet												

cage code 22526