


Rev	AWO #	Description	Date	Appr
-		RELEASED	4/1/15	

APPROVED: _____

DATE: _____ TITLE: _____







SECTION A–A

SPECIFICATIONS:
Material:
Insulator: PA66, rated UL 94V–0
Insulator color: Green
Screw: M2.0 Steel, Zinc plated
Clamp: Phosphor Bronze, Nickel plated
Cage: Brass, Nickel plated
Electrical:
Operation voltage: 300 V
Current rating: 8 A
Contact resistance: 20 mohms max
Insulation resistance: 500 Mohms min @ 500 VDC
Dielectric withstanding voltage: 2,000 VAC for 1 minute
Mechanical:
Wire Range: 16–28AWG, 1.0mm²
Torque: 0.2N–m, 1.7Lb–In
Wire strip length: 6–7mm
Temperature Rating:
Operating temperature: –40°C to +105°C
Environmental:
Lead free, RoHS compliant.

RoHS COMPLIANT

Positions: 2 thru 24
A= .138 [3.50] x No. of Spaces + .169 [4.30]
B= .138 [3.50] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	AY	4/1/15
CHECKED	NP	4/1/15
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: EURO BLOCK, .138 [3.50] PITCH

SIZE	PART NO.	REV.
X	EB5A-XX-A	-

REF: S00067C | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.