Part Number : 194390002
Product Description : Loxon Locking Quick Disconnect, Female, for 18-20 Wire, Tab 6.35 x 0.81mm, Carton
Series Number : 19439
Status : Active
Product Category : Quick Disconnects
Engineering Part Number : AA-4150



Documents and Resources

Drawings

194390002_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19439
Description	Loxon Locking Quick Disconnect, Female, for 18-20 Wire, Tab 6.35 x 0.81mm, Carton
Product Name	Loxon
Style	Locking Terminal
Type	Loxon Locking Disconnect
UPC	193264611706

Agency

UL	E79133

Electrical

Voltage - Maximum	600V AC

Physical

Barrel Type	Closed
Gender	Female
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.789/g
Orientation	Straight
Packaging Type	Carton
Plating min - Mating	2.540µm

Downloaded from Arrow.com.

Plating min - Termination	2.540µm
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-40° to +149°C
Wire Insulation Diameter	2.55-2.85mm
Wire Size (AWG)	18, 20

Mates With / Use With

Use with Part(s)

Description	Part Number
Loxon Locking Quick Disconnect Housing, Nylon, UL94V-2, Natural	194390007
Loxon Locking Quick Disconnect Housing, Nylon, UL94V-0, Natural	194390008

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Locking Quick Disconnect Crimp Terminals, 20-18 AWG	2133094100

Downloaded from Arrow.com.