



Part Number : [2066490001](#)
Product Description : 698MHz-960MHz Cellular
Ceramic Antenna, Low-profile, SMT
Series Number : 206649
Status : Active
Product Category : Antennas



Documents & Resources

Drawings

[2066490001_sd.pdf](#)
[2066490001-PK.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[2066490001-AS.pdf](#)
[2066490001-PS.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Antennas
Series	206649
Description	698MHz-960MHz Cellular Ceramic Antenna, Low-profile, SMT
Component Type	Surface Mount Device Antenna
Function	Signal
Product Name	698-960MHz Ceramic SMT Antenna
Protocol	Cellular
Type	Cellular Antenna, Internal, LPWAN
UPC	191128861243

Electrical

Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	698
Electrical Connectivity	SMD
Peak Gain (dBi)	0.5 @ 698 MHz, 0.8 @ 791 MHz, 0.9 @ 698 MHz, 1.1 @ 824 MHz
Return Loss - S11 (dB)	< -4, < -5, < -6, < -7
Total Efficiency	50% @ 698 MHz, 50% @ 791 MHz, 55% @ 698 MHz, 55% @ 824 MHz

Physical

Cable Length	N/A
Length	20.00mm
Mounting Style	Surface Mount
Net Weight	0.712/g
Packaging Type	Embossed Tape on Reel
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	1.20mm
Width	10.00mm

This document was generated on Sep 10, 2025