




PIN	A	B	C	D
9	16.92	24.99	30.84	11.86
15	25.50	33.32	39.24	19.50
25	38.96	47.04	53.04	32.15
37	55.42	63.50	69.62	48.76



PIN	A	B	C	D
9	16.33	24.99	30.84	11.86
15	24.76	33.32	39.24	19.50
25	38.33	47.04	53.04	32.15
37	54.89	63.50	69.62	48.76



10141449 - 09 P D 4 X LF

SERIES NO. _____

NUMBER OF CONTACTS _____

09: 09 PIN
15: 15 PIN
25: 25 PIN
37: 37 PIN

TYPE _____

P: PLUG (MALE)
S: SOCKET (FEMALE)

LF: ROHS COMPLIANT
DIMPLES
X: ON MALE CONNECTOR ONLY

PERFORMANCE CLASS
4: 200 MATING CYCLES

TERMINATION TYPE
D: IDC TYPE

6	Rivet	2	C3602	30u" copper base, 50u" Nickel plating
5	Rear Cover	1	PBT+30%G, F(UL94V-0)	BLACK
4	Housing	1	PBT+30%G, F(UL94V-0)	BLACK
3	Housing	1	PBT+30%G, F(UL94V-0)	BLACK
2	Contact	9	C2680	Contact area Plating Au: 30u" Nickel Plating: 30u"Min., Tin 100u" min.
1	Shell	1	SPCC	80u" copper base, 50u" Nickel plating
No.	Name	Qty	Material	SPEC.

mat'l. code		surface	tolerance	projection	product family	
		ISO 1302	ISO 406 ISO 1101		D-SUB	
ltr	ecn no	dr	date	tolerances unless otherwise specified		title
A	-	GREGAR	07/14/18	angles	.0±.4	D-SUB IDC CONNECTORS DIDC GM BLACK CRIMP
B	ELX-I-32435	GREGAR	10/01/19	linear	.00±.3	
C	ELX-N-40285	MXK	11/09/20	0°±2'	.000±.15	
				dr	GREGAR MATHEW 07/14/18	dwg no sheet 1 of 1 size
				enr	MITHUN PAUL 07/14/18	
				chr	MITHUN PAUL 10/01/19	
				appd	BIJU K PARUL 10/01/19	
sheet	revision	C				type Product Customer Drawing
index	sheet	1				