







PCB Layout(Bottom View)



N = Number of poles Δ

Dim A=Nx6.35+1.0

Dim B=(N-1)x6.35

Poles	Tol.	Dim A&B
2-5p		± 0.20
6-10p		± 0.25
11-16p		± 0.35
17-24p		± 0.40
25-30p		± 0.50

SIGN	DATE	DESCRIPTION	APPROVER
Δ	10/20'08	Add APPROVAL: : CQC	Kind
Δ	12/05'12	Change the screw plating specification	Jacky
Δ	12/05'12	Change the dimensional tolerance	Jacky
Δ	12/12'13	Add the view	Jacky
Δ	12/12'13	Change the withstand voltage and current	Jacky

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

MATERIALS ELECTRICAL	cULus	CQC
Δ RATED VOLTAGE & CURRENT:	250 V, 10 A	/ 250 V, 9 A
WITHSTAND VOLTAGE:	AC 2000 V/Min	
INSULATION RESISTANCE:	1000 M Ω OR MORE AT DC 500 V	
OPERATING TEMPERATURE RANG:	-40 $^{\circ}$ C ~ +115 $^{\circ}$ C	
SCREW TORQUE VALUE:	5.3 Lb-In.	
WIRE RANGE:	22 - 18 AWG	
1) MOLDED PARTS:	Thermoplastic, UL 94 V-0 BLACK	
2) TERMINAL:	BRASS, 0.8t, Tin PLATED	
Δ 3) TERMINAL SCREWS:	STEEL, M3	
Δ 1) APPROVAL:	 	
PART NO.:		
Critical dimension:	Δ	

YK 221 xx 0 x x 00G

NO. OF POLES
02: 2 POLES
03: 3 POLES
04: 4 POLES
:
30: 30 POLES

G: RoHS compliant
(lead<4%) In copper Alloy
MARK
0: "@" MARK
1: "ANY" MARK

TERMINAL & SCREW PLATED
0: TERMINAL & SCREW: G/F
 Δ 1: TERMINAL: G/F, SCREW: Zinc
2: TERMINAL: Sn, SCREW: G/F
 Δ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-221 Series							
PART NO.	YK221xx0xx00G				DWG NO.	8YK0001-221		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Jacky 2013.12.12	Jacky 2013.12.12		UNIT: mm		X.	±0.50
					SCALE: NONE		X.X	±0.30
					REV.: G		X.XX	±0.10
					SHEET: 01/01		X°	±1°

SHEET: 01/01

REV.: G