



ZCM Series Datasheet

SMD Precision Metal Film Resistors | MELF Style

ORDERING CODE-Example

New SAP Part Nr.:

ZCM	207	F	K	E	07-	1K	AA
Serie	Power rating 204 = 0,4W 207 = 1,0W	Tol. B = ±0,1% C = ±0,25% D = ±0,5% F = ±1% G = ±2% J = ±5%	Pack-Code K = Blister tape reel	TCR C = ±15ppm D = ±25ppm E = ±50ppm F = ±100ppm	Forming type 07- = 07 inch (Reel diameter) or 13- = 13 inch (Reel diameter)	R Value	Special AA = Standard

Historical VTM Part Nr.:

ZC	0207	F	K	E	07	1K
Type	Size	Tol.	K = Blister tape reel	TC	Reel diam.	R Value

APPLICATIONS

- Automotive
- Charger
- Alternative Energy
- Power Supply
- Home Appliances
- Industrial



FEATURES

- Precision MELF resistor
- Advanced MELF technology
- Excellent stability in different environmental conditions
- Best in class pulse load capability
- AEC – Q200 Qualified
- Intrinsic sulfur resistance
- RoHs & REACH Compliant

ELECTRICAL SPECIFICATIONS

Type		ZCM204	ZCM207
Historical Part Number	SMD	ZC0204	ZC0207
Nominal Power Rating P_{70}	[W]	0,4	1,0
Resistance Range	[Ω]	0R22 ... 10M	0R16 ... 10M
		(Other values upon request)	
E-Series		E24 / E96 / E192	
Tolerances	±[%]	B = 0,1% , C = 0,25% , D = 0,5% , F = 1% , G = 2% , J = 5%	
Temperature Coefficient IEC60115-1 clause 4.2 ; 4.8 (+20 / -55[°C] and (+20 / +125[°C]))	±[10 ⁻⁶ * K ⁻¹]	Depends on the value, please check the table below	
Working Temperature Range	[°C]	-55 ... +155	
Permissible film temperature (9F max.)	[°C]	155	
Max. Working Voltage	[AC or DC] _{RMS}	200	350
Dielectric Withstanding Voltage IEC115-1 clause 4.7 (1[min])	[V] _{RMS}	300	500

DIMENSIONS [mm]



Type	Historical P/N:	L	Ø D	L ₁	Ø D ₁	A	MASS (mg)
ZCM204	ZC0204	3,6 +0/-0,2	1,4 +0/-0,1	1,8 min.	D +0/-0,15	0,80 ±0,10	22
ZCM207	ZC0207	5,8 +0/-0,3	2,2 ±0,2	2,6 min.	D +0/-0,2	1,25 ±0,2	77

Recommended solder pads dimensions								
Type	Wave soldering				Reflow soldering			
	l	a	b	c	l	a	b	c
ZCM204	1,5	1,5	1,8	4,5	1,7	1,2	1,6	4,1
ZCM207	2,4	2,3	2,6	7,0	2,6	2,0	2,4	6,6

ZCM Series Datasheet

PERFORMANCE DATE

Type			ZCM204	ZCM207
Historical Part Number			ZC0204	ZC0207
Climatic Category			55/155/56	
Short Time Overload IEC60115-1 clause 4.13 ($U=2,5 \cdot \sqrt{P_{10} \times R} \cdot \leq 2 \cdot U_{max, 5 [s]}$)	Standard operation	±[%]	0,03 (≤1M) ; 0,1 (>1M)	0,03 (≤1M) ; 0,15 (>1M)
	Power operation		0,05 (≤1M) ; 0,1 (>1M)	0,05 (≤1M) ; 0,15 (>1M)
Single pulse high voltage overload IEC60115-1 clause 4.27 ($U=10 \cdot \sqrt{P_{10} \times R}$, Severity 4, 10 pulses 10[μs]/700[μs])	Standard operation	±[%]	0,15	0,25
	Power operation		0,15	0,5
Periodic electric overload IEC60115-1 clause 4.39 ($U=15 \cdot \sqrt{P_{10} \times R}$, 0.1[s]on, 2.5[s]off, 1000 cycles)	Standard operation	±[%]	0,15	0,15
	Power operation		0,3	0,3
Failure Rate (Total, 90, max, 60[%] cont. lev.)		[10 ⁻⁹ h ⁻¹]	≤ 0,1	
Endurance at 70°C, IEC60115-1 clause 4.25.1 ($U=\sqrt{P_{10} \times R} \cdot U_{max, 1,5[h]ON ; 0,5[h]OFF}$)	Precision operation	±[%]	1000h	0.05 (10R≤1M)
			8000h	0.1 (10R≤1M)
	Standard operation	±[%]	1000h	0.15 (<10R) ; 0.1 (10R≤1M) ; 0.25 (>1M)
			8000h	0.3 (<10R) ; 0.2 (10R≤1M) ; 0.5 (>1M)
	Power operation	±[%]	1000h	0.25 (≤1M) ; 0.5 (>1M)
			8000h	0.5 (≤1M) ; 1 (>1M)
Endurance at upper Category Temp. IEC60115-1 clause 4.25.3 (1000[h])		±[%]	125°C	0.15 (<10R) ; 0.1 (10R≤1M) ; 0.25 (>1M)
			155°C	0.3 (<10R) ; 0.2 (10R≤1M) ; 0.5 (>1M)
Damp Heat, Steady State IEC60115-1 clause 4.24 (40 ^{±2} [°C], 93 ^{±3} [% r.h.], 56[d])		±[%]	0,15 (≤ 1M) ; 0,25 (>1M)	0,25 (≤ 1M) ; 1 (>1M)
Damp Heat, Steady State, Accelerated IEC60115-1 clause 4.37 (85 ^{±2} [°C], 85 ^{±5} [%RH], $U = 0.3 \cdot \sqrt{P_{10} \times R}$)		±[%]	0,25 (≤ 1M) ; 2 (>1M)	0,5 (≤ 1M) ; 2 (>1M)
Temperature Cycling IEC60068-2-14 ; IEC60115-1 clause 4.19 (30[min] each, 1000 cycles)	±[%]	-55~125°C	0,15 (≤ 1M) ; 0,25 (>1M)	0,25
		-55~155°C	0,5	0,5
Vibration IEC60068-2-6 ; IEC60115-1 clause 4.22 (10;2000[Hz], ≤1,5[mm], or ≤200[m/s ²] 7,5[h])		±[%]	0,05 (≤ 1M) ; 0,1 (>1M)	0,05
Resistance to Soldering Heat IEC60115-1 clause 4.18 (260 ^{±5} [°C], 10 ^{±1} [s]) Solder bath method		±[%]	0,1 (≤ 10R) ; 0,05 (>10R)	0,1 (≤ 10R) ; 0,05 (>10R)
Electrostatic Discharge IEC60115-1 clause 4.38 ; IEC61340-3-1 (3 positives + 3 negatives discharges)		±[%]	0,5 [2 kV]	0,5 [4 kV]
Voltage proof IEC60115-1 clause 4.7 $U_{RMS}=U_{INS}$, 60 [s]			No flash over or breakdown	
Flammability IEC60115-1 clause 4.35, IEC60695-11-5 Needle flame test, 10[s]			No burning after 30[s]	
Solderability IEC60068-2-20 ; IEC60115-1 clause 4.17 (235 ^{±5} [°C] 2 ^{±0,2} [s], SnAg ₃ Cu _{0,5} or SnAg _{3,5})			≥ 95% covered, no visible damage	
Component Resistance to Solvents IEC60068-2-45 ; IEC60115-1 clause 4.29 (50[°C] method 2)			No visible damage	
Resistance to solvents of Marking IEC60068-2-45 ; IEC60115-1 clause 4.30 (50[°C] method 1)			Marking visible, no visible damage	
Marking IEC60062			Color code	

NOTES: MARKING [COLOR CODE]:

- **ZCM204** Color code marking is applied according to IEC 60062 in four bands (E24 series) for 5 % tolerance, or in five bands (E96 or E192 series). Each color band appears as a single solid line, voids are permissible if at least 2/3 of the band is visible from each radial angle of view. The last color band for tolerance is approximately 50 % wider than the other bands.
 - **ZCM207** Color code marking is applied according to IEC 60062 in four (E24 series) or six bands (E96 series). Each color band appears as a single solid line, voids are permissible if at least 2/3 of the band is visible from each radial angle of view. The last color band represents the TCR for resistors with TCR ≤50 ppm/K and nominal tolerance ≤1 %.
- Zero ohm jumpers are marked with one centered black band.

ZCM Series Datasheet

TEMPERATURE COEFFICIENT

ZCM204	ZCM207			
Resistance range		Tolerance	TCR	E-Series
0R22 ... 0R91	0R16 ... 0R91	± 5%	± 100 ppm/K	E24
	0R22 ... 0R91	± 2%		
0R82... 10M	1R... 10M	± 1%	± 50 ppm/K	E24 / E96
10R... 1M65	1R... 2M21	± 0,5%		
10R... 1M65	43R... 1M	± 0,5%	± 25 ppm/K	E24 / E192
22R... 1M65	43R... 1M	± 0,25%		
22R... 1M65	43R... 1M	± 0,1%	± 15 ppm/K	E24 / E192
10R... 221K	100R... 511K	± 0,5%		
22R... 221K	100R... 511K	± 0,25%		
43R... 221K	100R... 511K	± 0,1%		
Jumper $I_{max} = 3A$	Jumper $I_{max} = 5A$	≤ 10 mΩ		

- The body coating color is light green for jumpers and for a temperature coefficient of ±50 or 100 [ppm], pink for ±25[ppm] and violet for ±15[ppm]


MAXIMUM RESISTANCE CHANGE AT RATED DISSIPATION

		ZCM204			ZCM207		
OPERATION MODE		PRECISION	STANDARD	POWER	PRECISION	STANDARD	POWER
Rated Power dissipation P ₇₀ [W]		0,07	0,25	0,4	0,125	0,4	1,0
Operating temp. range [°C]		-10 to 85	-55 to 125	-55 to 155	-10 to 85	-55 to 125	-55 to 155
Permissible film temperature θF Max [°C]		85	125	155	85	125	155
Resistance range		10R – 1M	R22 – 1M	R22 – 10M	100R – 511K	1R0 – 1M	1R0 – 1M
Max. Resistance drift [%] [ΔR/R]	1000h	≤0,05	≤0,15	≤0,25	≤0,05	≤0,15	≤0,25
	8000h	≤0,1	≤0,3	≤0,5	≤0,1	≤0,3	≤0,5
	225 000h	≤0,25	≤0,75	-	≤0,25	≤1,0	-


- A suitable low thermal resistance of the circuit board assembly must be safeguarded in order to maintain the film temperature of the resistors within the specified limits.

PERFORMANCE GRAPH'S


Derating – Precision Operation




Derating – Standard Operation



Derating – Power Operation




Non- Linearity




ZCM Series Datasheet


Current Noise




Pulse Voltage




Single Pulse for $R < 10\Omega$




Continuous Pulse for $R < 10\Omega$




Single Pulse for $R \geq 10\Omega$




Continuous Pulse for $R \geq 10\Omega$



Single Pulse (1.2/50 [μs])



Single Pulse (10/700 [μs])



ZCM Series Datasheet

PACKAGING - Blister tape

The type ZCM is packed in antistatic blister tape according to IEC60286-3, type 2a, packing details described below,

