

Part Number: APBD3224LSURKCGKC

Hyper Red  
Green




### Features

- 3.2x2.4mm SMD LED, 2.4mm thickness.
- Low power consumption.
- Ideal for backlight and indicator.
- Package : 1500pcs / reel.
- Moisture sensitivity level : level 3.
- Low current IF=2mA operating.
- RoHS compliant.

### Descriptions

- The Hyper Red source color devices are made with Al GaInP on GaAs substrate Light Emitting Diode.
- The Green source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode.

### Package Dimensions



#### Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is ±0.1(0.004") unless otherwise noted.
3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
4. The device has a single mounting surface. The device must be mounted according to the specifications.



## Selection Guide

| Part No.          | Emitting Color (Material) | Lens Type   | Iv (mcd) [2]<br>@ 2mA |      | Viewing<br>Angle [1] |
|-------------------|---------------------------|-------------|-----------------------|------|----------------------|
|                   |                           |             | Min.                  | Typ. |                      |
| APBD3224LSURKCGKC | Hyper Red (AlGaInP)       | Water Clear | 20                    | 50   | 20°                  |
|                   |                           |             | *10                   | *30  |                      |
|                   | Green (AlGaInP)           |             | 10                    | 30   |                      |
|                   |                           |             | *10                   | *30  |                      |

### Notes:

1.  $\theta_{1/2}$  is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.

2. Luminous intensity / luminous Flux: +/-15%.

\* Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

## Electrical / Optical Characteristics at TA=25°C

| Symbol                | Parameter                | Emitting Color     | Min.       | Typ.        | Max.       | Units | Test Conditions            |
|-----------------------|--------------------------|--------------------|------------|-------------|------------|-------|----------------------------|
| $\lambda_{peak}$      | Peak Wavelength          | Hyper Red<br>Green |            | 645<br>574  |            | nm    | I <sub>F</sub> =2mA        |
| $\lambda_D$ [1]       | Dominant Wavelength      | Hyper Red<br>Green |            | 630<br>570  |            | nm    | I <sub>F</sub> =2mA        |
| $\Delta\lambda_{1/2}$ | Spectral Line Half-width | Hyper Red<br>Green |            | 28<br>20    |            | nm    | I <sub>F</sub> =2mA        |
| C                     | Capacitance              | Hyper Red<br>Green |            | 35<br>15    |            | pF    | V <sub>F</sub> =0V; f=1MHz |
| V <sub>F</sub> [2]    | Forward Voltage          | Hyper Red<br>Green | 1.5<br>1.5 | 1.75<br>1.9 | 2.1<br>2.1 | V     | I <sub>F</sub> =2mA        |
| I <sub>R</sub>        | Reverse Current          | Hyper Red<br>Green |            |             | 10<br>10   | uA    | V <sub>R</sub> = 5V        |

### Notes:

1.Wavelength: +/-1nm.

2. Forward Voltage: +/-0.1V.

3.Wavelength value is traceable to the CIE127-2007 compliant national standards.


4.Excess driving current and/or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.

## Absolute Maximum Ratings at TA=25°C

| Parameter                | Hyper Red      | Green | Units |
|--------------------------|----------------|-------|-------|
| Power dissipation        | 63             | 63    | mW    |
| DC Forward Current       | 30             | 30    | mA    |
| Peak Forward Current [1] | 185            | 150   | mA    |
| Reverse Voltage          | 5              |       | V     |
| Operating Temperature    | -40°C To +85°C |       |       |
| Storage Temperature      | -40°C To +85°C |       |       |





### Note:

1. 1/10 Duty Cycle, 0.1ms Pulse Width.








Relative Intensity Vs. Wavelength

## APBD3224LSURKCGKC Hyper Red




Green



## APBD3224LSURKCGKC

Reflow soldering is recommended and the soldering profile is shown below.  
Other soldering methods are not recommended as they might cause damage to the product.


Reflow Soldering Profile For Lead-free SMT Process.




### NOTES:

1. We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.
2. Don't cause stress to the epoxy resin while it is exposed to high temperature.
3. Number of reflow process shall be 2 times or less.


### Recommended Soldering Pattern (Units : mm; Tolerance: $\pm 0.1$ )



### Reel Dimension




### Tape Dimensions (Units : mm)



## PACKING & LABEL SPECIFICATIONS

APBD3224LSURKCGKC



|                                                                                     |                                                                                                          |     |            |        |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------|-----|------------|--------|
| <b>Kingbright</b>                                                                   |                                                                                                          |     |            |        |
| P/NO: APBD3224xxx                                                                   |                                                                                                          |     |            |        |
| QTY: 1,500 pcs                                                                      | Q.C. <table border="1"><tr><td>Q C</td></tr><tr><td>xx xx xxxx</td></tr><tr><td>PASSED</td></tr></table> | Q C | xx xx xxxx | PASSED |
| Q C                                                                                 |                                                                                                          |     |            |        |
| xx xx xxxx                                                                          |                                                                                                          |     |            |        |
| PASSED                                                                              |                                                                                                          |     |            |        |
| S/N: XXXX                                                                           |                                                                                                          |     |            |        |
| CODE: XXX                                                                           |                                                                                                          |     |            |        |
| LOT NO:                                                                             |                                                                                                          |     |            |        |
|  |                                                                                                          |     |            |        |
| RoHS Compliant                                                                      |                                                                                                          |     |            |        |

### Terms and conditions for the usage of this document

1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.
2. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
6. All design applications should refer to Kingbright application notes available at <http://www.KingbrightUSA.com/ApplicationNotes>