


VICOR CONFIDENTIAL

THIS DOCUMENT AND THE DATA DISCLOSED HEREIN OR HERewith IS NOT TO BE REPRODUCED, USED, OR DISCLOSED IN WHOLE OR IN PART TO ANYONE WITHOUT PERMISSION OF VICOR CORP.

REV.	DESCRIPTION	DATE	APPROVED
1	RELEASED PER E060753	GCK 6/21/06	SH



ELECTRICAL CHARACTERISTICS @ T=20°C (UNLESS OTHERWISE SPECIFIED)

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	TEST CONDITIONS
CAPACITANCE	C	376	470	564	μ F	@ 120 Hz, 20°C
WORKING VOLTAGE	V _{DCW}	450			V	
SURGE VOLTAGE	V surge			500	V	
LEAKAGE CURRENT	I _{DCL}			3	mA	@ 20°C, 5 MINUTES @ RATED VOLTAGE
DISSIPATION FACTOR	DF			0.15		
EQUIVALENT SERIES RESISTANCE	ESR			.529	Ω	@ 120 Hz, 20°C
RIPPLE CURRENT	I _{RMS}			1.78	A	@ 120 Hz, +105°C
OPERATING TEMPERATURE	T _{OP}	-25°C - +105°C			°C	

MARKING:

MFG. ID/PF CODE

- NOTES:
1. RoHS COMPLIANT, LEAD FREE PER CST-0001 LATEST REVISION.
 2. NEGATIVE MAY BE SHOWN BY EITHER MARKING.
 3. DIMENSIONS ARE IN INCHES [MM]

DRAWN BY <i>P.E.IENI</i>	DATE 08/03/05				
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES- TOLERANCES ARE: FRACTIONS DECIMALS ANGLES +1/64 .XX=+.01 ±1° .XXX=+.005		CAPACITOR ALEL 470uF ±20 450V			
THIRD ANGLE PROJECTION 	SIZE B	FSCM NO. 67131	DWG NO 30249	REV 1	
DO NOT SCALE DRAWING		SCALE	SHEET 1 OF 1		