

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0470184001

Status:


Active

Overview:

Serial ATA Connectors

Description:

1.27mm Pitch Serial ATA Host Receptacle, Mating Height 5.15mm, 0.76µm Gold (Au) Plating, Light Tin Solder Area, Surface Mount, Right-Angle, Top Mount Type, 22 Circuits, Lead-Free



Documents:	
3D Model	Product Specification PS-67492-001-007 (PDF)
3D Model (PDF)	Packaging Specification PK-47018-003-002 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-67492-001-001 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Receptacles
Series	47018
Application	Board-to-Board, Signal
Comments	Top Mount Type
Overview	Serial ATA Connectors
Product Name	Serial ATA
UPC	822350330824
Physical	
Circuits (Loaded)	22
Circuits (maximum)	22
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	1.750/g
Number of Rows	1
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.032µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-35° to +85°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	1.5A

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

47018 Series

Mates With

877030001

Voltage - Maximum	15V DC
Solder Process Data	
Lead-freeProcess Capability	REFLOW
Process Temperature max. C	230
Material Info	
Reference - Drawing Numbers	
Electrical Model Document	EE-47018-003-001
Packaging Specification	PK-47018-003-002
Product Specification	PS-67492-001-001, PS-67492-001-007
S-Parameter Model	SP-47018-003-001
Sales Drawing	SD-47018-001-001

This document was generated on 08/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION