

P/N: T197914

Copyright

© 2020, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: T197914

Commit: 42932

Language: en-US

Modified: 2017-05-30

Formatted: 2020-06-17

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.



General description

The 15° lens is a popular lens accessory and provides 1.7× magnification compared to the standard lens. Ideal for small or distant targets such as overhead power lines.

Imaging and optical data

Field of view (FOV)	15° × 11° (19° diagonally)
Minimum focus distance	500 mm (19.69 in.)
Focal length	41.3 mm (1.63 in.)
Spatial resolution (IFOV)	0.41 mrad
Lens identification	Automatic
F-number	1.0
Number of lenses	3 (3 asph)
MTF @ 70% of FOV	Normal requirements (52%)
Distortion	3%

Physical data

Weight	0.190 kg (0.419 lb.)
Size (L × D)	47 × 67 mm (1.85 × 2.64 in.)
Front lens diameter	52 mm (2.05 in.)

Shipping information

Packaging, type	Cardboard box
List of contents	<ul style="list-style-type: none"> • Lens • Lens case • Front lens cap • Rear lens cap
Packaging, weight	0.427 kg (0.95 lb.)
Packaging, size	174 × 133 × 133 mm (6.85 × 5.24 × 5.24 in.)
EAN-13	7332558004449
UPC-12	845188002671
Country of origin	Sweden

Compatible with the following products:

- 55001-0101; FLIR A615 15°
- 55001-0102; FLIR A615 25°
- 55001-0103; FLIR A615 45°
- 55001-0104; FLIR A615 7°



IR lens, f=41.3 mm (15°) with case







P/N: T197914

© 2020, FLIR Systems, Inc.

#T197914; r. 42932; en-US





- 55001-0105; FLIR A615 80°
- 55001-0301; FLIR A655sc 15°
- 55001-0302; FLIR A655sc 25°
- 55001-0303; FLIR A655sc 45°
- 55001-0304; FLIR A655sc 7°
- 55001-0305; FLIR A655sc 80°

Camera with Lens IR f=41,3 mm (15°)



For additional dimensions see page 1			
Modified 2012-04-19	Check CAHA	Drawn by R&D Thermography	FLIR®
Denomination			
Basic dimensions FLIR T6xx			
Size A3	Scale 1:2	Sheet 5(9)	Size A
Drawing No. T127424			

Camera with Lens IR f=41,3 mm (15°)



For additional dimensions see page 1

FLIR®		Drawing No. T126925		Size A	
A3		Scale 1:2		Sheet 5(9)	
Size		Drawing No.		Size	

Modified 2012-04-18		Check CAHA		Drawn by R&D Thermography	
Denomination		Basic dimensions FLIR A/SC 6xx			