


40014000440 - 400 Series



Series: 400

Questions? [Contact Littelfuse Support](#)

[Fuse 400 Datasheet](#)

The Littelfuse 400 Series is a TE5® Time Lag Fuse with High Breaking Capacity.

Features:

- Operating temperature: -40°C to 125°C
- Higher nominal melting I²T
- Higher interrupt rating
- Broad current rating 500mA to 6.3A
- Lead-Free, Halogen-Free, Compliance with RoHS
- Shock safe casing

Applications:

- SMPS for NB, printers, adaptors, consumer electronics, industrial controllers, battery chargers

[Check Stock](#)

[Order Samples](#)

NEW!
Product Selection Guide eCatalog

[Read Now](#)

Electronics
News and Information

[SIGN UP NOW](#)

[Feedback](#)

Electrical Characteristics	Technical Resources	Environmental Info
Property (Mouseover for details)	Value	
Ampere Rating (A)	4	
Nominal Melting I²T (A²sec)	133.4	
Interrupting Rating	130A@250VAC	
Min Operating Temp °C	-40	
Max Operating Temp (°C)	85	
Nominal Power Dissipation (W)	936	
Nominal Voltage Drop (mV)	65	
Opening	Slo-Blo/Time Lag (T)/Time Delay	
Package Size	TE5 (8.5x8mm)	
VAC (V)	250	

Connect with Littelfuse

Sign up to receive special offers and news

[Submit](#)

For more details about how we use your information, check our [Privacy Statement](#).

[Mobile Site](#)

About Littelfuse

[About Littelfuse](#)

[Conflict Free Statement](#)

[History](#)

[Investor Relations](#)

[Legal](#)

[Press Room](#)

[Privacy Statement](#)

[Supply Chain Transparency](#)

[Website Feedback](#)

Explore Littelfuse

[Capabilities Brochures](#)

[Careers](#)

[Check Distributor Stock](#)

[Competitor Cross Reference](#)

[Industries](#)

[Order Samples](#)

[Products](#)

[Services](#)

Technical Resources

[Application Designs](#)

[Education](#)

[FAQs](#)

[iDesign™](#)

[Littelfuse University](#)

[Product Catalogs](#)

[Quality Documents](#)

[Technical Documents](#)