



Catalog No. TY635M

Description: CABLE TIE 50LB 8IN NAT NY MTG HOLE

UPC No 786210825526

Home > Wire & Cable Management > Ty-Rap > Mounted Head Ties

Integrated Mounting Hole Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 198mm (7.8 Inches), Width of 4.6mm (0.18 Inch), Thickness of 1mm (0.04 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds), #6 Screw for Mounting, Bulk Pack

Descriptors

Category	Mounted Head Ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds , 220 newtons

Classifications

Brand Name	Ty-Rap
------------	--------

Dimensions

Width	0.18 in , 4.6 mm
Length	7.8 in , 198 mm
Thickness	0.04 in , 1 mm
Bundle Diameter	0.12 to 4 in , 3 to 102 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM Classification

ETIM	EC000046 Cable tie
Band width	4.6 mm

by ABB

ETIM	EC000046 Cable tie
Length belt/tape/tie	198 mm
Length belt/tape/tie	7.8 inch
Tie thickness	1 mm
Tie thickness	0.04 inch
Max. bundle diameter	102 mm
Min. holding force	220 N
Operation temperature	-40-+85 °C
Operation temperature	-40-+185 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
Type of fastening	Screw hole
VG approval	N
MIL approval	N
UL approval	N