



DC COMPONENTS CO., LTD.
RECTIFIER SPECIALISTS

**1N4728A
THRU
1N4761A**

TECHNICAL SPECIFICATIONS OF GLASS SILICON ZENER DIODES

VOLTAGE RANGE - 3.3 to 75 Volts

POWER - 1.0 Watt

FEATURES


- * Voltage range : 3.3V to 75V
- * Double slug type construction

MECHANICAL DATA

- * Case: Glass sealed case
- * Terminals: Solder plated solderable per MIL-STD-750, Method 2026
- * Polarity: Color band denotes cathode end
- * Mounting position: Any
- * Weight: 0.35 gram

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS




Ratings at 25°C ambient temperature unless otherwise specified.
Single phase, half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.



	SYMBOL	VALUE	UNITS
Zener Current See Table "Characterisitics"			
Power Dissipation at T _A = 25°C	P _{tot}	1.0 ⁽¹⁾	W
Junction Temperature	T _J	200	°C
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C
Maximum Instantaneous Forward Voltage at I _F = 200 mA	V _F	1.2	Volts
Typical Thermal Resistance Junction to Ambient Air	R _{θJA}	170	°C/W

Note 1 : Suffix "A" indicates Zener Voltage Tolerance ± 5%

RATING AND CHARACTERISTIC CURVES (1N4728A THRU 1N4761A)



RATING AND CHARACTERISTIC CURVES (1N4728A THRU 1N4761A)

TYPE	Nominal Zener Voltage	Zener Test Current	Maximum Zener Impedance		IZK	Maximum Reverse Leakage Current	
	VZ@IZT	IZT	ZZT@IZT	ZZT@IZK		IR	@VR
	Volts	mA	Ohms	Ohms		μA	Volts
1N4728A	3.3	76	10	400	1.0	100	1.0
1N4729A	3.6	69	10	400	1.0	100	1.0
1N4730A	3.9	64	9.0	400	1.0	50	1.0
1N4731A	4.3	58	9.0	400	1.0	10	1.0
1N4732A	4.7	53	8.0	500	1.0	10	1.0
1N4733A	5.1	49	7.0	550	1.0	10	1.0
1N4734A	5.6	45	5.0	600	1.0	10	2.0
1N4735A	6.2	41	2.0	700	1.0	10	3.0
1N4736A	6.8	37	3.5	700	1.0	10	4.0
1N4737A	7.5	34	4.0	700	0.5	10	5.0
1N4738A	8.2	31	4.5	700	0.5	10	6.0
1N4739A	9.1	28	5.0	700	0.5	10	7.0
1N4740A	10	25	7.0	700	0.25	10	7.6
1N4741A	11	23	8.0	700	0.25	5.0	8.4
1N4742A	12	21	9.0	700	0.25	5.0	9.1
1N4743A	13	19	10	700	0.25	5.0	9.9
1N4744A	15	17	14	700	0.25	5.0	11.4
1N4745A	16	15.5	16	700	0.25	5.0	12.2
1N4746A	18	14	20	750	0.25	5.0	13.7
1N4747A	20	12.5	22	750	0.25	5.0	15.2
1N4748A	22	11.5	23	750	0.25	5.0	16.7
1N4749A	24	10.5	25	750	0.25	5.0	18.2
1N4750A	27	9.5	35	750	0.25	5.0	20.6
1N4751A	30	8.5	40	1000	0.25	5.0	22.8
1N4752A	33	7.5	45	1000	0.25	5.0	25.1
1N4753A	36	7.0	50	1000	0.25	5.0	27.4
1N4754A	39	6.5	60	1000	0.25	5.0	29.7
1N4755A	43	6.0	70	1500	0.25	5.0	32.7
1N4756A	47	5.5	80	1500	0.25	5.0	35.8
1N4757A	51	5.0	95	1500	0.25	5.0	38.8
1N4758A	56	4.5	110	2000	0.25	5.0	42.6
1N4759A	62	4.0	125	2000	0.25	5.0	47.1
1N4760A	68	3.7	150	2000	0.25	5.0	51.7
1N4761A	75	3.3	175	2000	0.25	5.0	56.0

Disclaimer

Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold **DC COMPONENTS** harmless against all damages.

DC COMPONENTS disclaims any and all liability arising out of the application or use of any product, including consequential or incidental damages. Statement regarding the suitability of products for certain types of applications are based on **DC COMPONENTS**'s knowledge of typical requirements that are often placed on **DC COMPONENTS** products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application.

DC COMPONENTS reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein, and disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product. Parameters provided in datasheets and specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify **DC COMPONENTS**'s terms and conditions of purchase, including but not limited to the warranty expressed therein.

Unless otherwise in writing, **DC COMPONENTS** products are intended for use as general electronic components in standard applications (eg: Consumer electronic, Computer equipment, Office equipment, etc.), and not recommended for use in a high specific application where a failure or malfunction of the device could result in human injury or death (eg: Aerospace equipment, Submarine cables, Combustion equipment, Safety devices, Life support systems, etc.)

Customers using or selling **DC COMPONENTS** products not expressly indicated for use in such applications do so at their own risk. If customer intended to use **DC COMPONENTS** standard quality grade devices for applications not envisioned by **DC COMPONENTS**, please contact our sales representatives in advance.