

Product data sheet

Specifications



APC Symmetra LX 8kVA Scalable to 16kVA N+1 Rack-mount, 220/230/240V or 380/400/415V

SYA8K16RMI

Overview

Presentation	High performance, redundant power protection with scalable power and runtime for space-constrained server rooms, and voice and data networks.
Lead time	Usually in Stock

Main

Main Input Voltage	220 V AC 1 phase 400 V AC 3 phases 230 V AC 1 phase 240 V AC 1 phase 380 V AC 3 phases 415 V AC 3 phases
Product or component type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V 380 V 415 V
Main Output Voltage	220 V AC 1 phase 230 V AC 1 phase 240 V AC 1 phase
Other Output Voltage	220 V 240 V
Rated power in W	5600 W
Rated power in VA	8000 VA
output connection type	8 IEC 60320 C13 10 IEC 60320 C19
Output connector type	Hard wire 3-wire (H N + E) 1
Number of rack unit	19U
Battery type	Lead-acid battery
Provided equipment	CD with software Documentation CD Installation guide User manual Web/SNMP management card
Range of product	Symmetra LX

Complementary

Battery type	Lead-acid internal included
UPS connectivity	Serial port Available expansion slot Pre-installed network management card 3
Mounting mode	Rack-mounted with included kit

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Batteries & Runtime

Run Time	View Runtime Graph 
Number of battery filled slots	2
Number of battery free slots	2
Battery recharge time	3 h
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Battery charger power	574 W rated
Battery life	3...5 year(s)
Extended runtime	1

General

product web sub-family	4kVA power increments
Number of power module free slots	3
Number of power module filled slots	2
Redundant	Yes

Physical

Colour	Black Silver
Height	838 mm
Width	472 mm
Depth	688 mm
Net weight	198.64 kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	No

Input

Network frequency	45...65 Hz auto-sensing
Number of input connectors	1 hard wire 3-wire (1P + N + E) 1 hard wire 5-wire (3P + N + E)
Input voltage limits	155...276 V 290...480 V 3:1
Input harmonic distortion	Less than 7 % for full load
Input Power Factor at Full Load	0.98

Output

Maximum configurable power in W	11200 W
Harmonic distortion	Less than 5 % at full load
Output frequency	47...63 Hz sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal unsynchronised 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised

Crest factor	Up to 5 : 1
UPS type	Double conversion online
Wave type	Sine wave
Bypass type	Internal bypass (automatic and manual)
Efficiency	90 % (full load)
Maximum output current	36 A
Maximum configurable power in VA	16000 VA

Conformance

Product certifications	C-Tick CE GOST VDE
Standards	EN 50091-1 EN 50091-2 EN 55022 class A EN 55024 EN 60950 IEC 60950

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0...4572 m
Acoustic level	62 dBA
Heat dissipation	3707 Btu/h

Communications & Management

Free slots	1
Preinstalled device	Network management card 2 with environmental monitoring
Control panel	Multifunction LCD status and control console
Alarm	Audible and visible alarms : prioritized by severity
Emergency power off	Yes

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	105.4 cm
Package 1 Width	59.9 cm
Package 1 Length	99.7 cm
Package 1 Weight	239.55 kg

Contractual warranty

Warranty

2 years repair or replace

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Total lifecycle Carbon footprint	36290

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
REACH Regulation	REACH Declaration

Energy efficiency

Energy Efficiency Optimized	Energy efficient product
-----------------------------	--------------------------

Use Again

Repack and remanufacture	
Removable battery	User replaceable
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative









