


SmartRack 12U Server-Depth Wall-Mount Small Rack Enclosure, Clear Acrylic Window, Hinged Back

MODEL NUMBER: **SRW12US33G**



Wall-mount cabinet secures and organizes 12U of 19-inch rack equipment in network closets, classrooms and other locations with limited floor space. Extra deep to accommodate 1U servers, UPS systems, battery packs and switches.

Description

The SRW12US33G SmartRack 12U Server-Depth Wall-Mount Rack Enclosure Cabinet is ideal for storing 19-inch rack equipment up to 32.5 inches in depth in areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 250 lbs (113.4 kgs).

The front door features a shatter-resistant clear acrylic window that lets you monitor equipment readouts without unlocking the enclosure. Not only does the window help prevent equipment tampering and reduce acoustic noise, but it also adds visual flair to your IT installation.

The cabinet swings away from the wall on a sturdy hinge, allowing easy access to equipment and cabling during installation and maintenance. To ensure your valuable equipment stays secure, the doors and side panels lock. The top, bottom and removable side panels are vented, which allows air to flow freely through the rack to keep equipment cool. The reversible doors can open left or right by rotating the cabinet 180° before mounting. Convenient top and bottom ports allow easy cable routing through the cabinet.

The SRW12US33G comes fully assembled and ready to mount to the wall. Square and 12-24 threaded mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails adjust in 7/8-inch increments to accommodate equipment up to 32.5 inches, such as 1U servers, UPS systems, battery packs and switches.

Features

Saves Valuable Workspace Perfect for network closets, retail locations, classrooms and other areas with limited floor space where you need equipment to be secure, organized and out of the way
Extra-deep capacity to house most 1U servers, UPS systems, battery packs and switches
Maximum load capacity of 250 pounds (113.4 kg)

Hinged Cabinet for Convenient Access Swings away from the wall to allow easy access to equipment and cabling during installation and maintenance
Rotate cabinet 180° before mounting to open reversible front door left or right

Shatter-Resistant Clear Acrylic Front Window Lets you monitor equipment without unlocking the enclosure
Prevents equipment tampering
Reduces acoustic noise
Provides extra visual flair

Keeps Important Equipment Secure Side panels and doors lock securely
Vented panels allow generous airflow that keeps equipment cool
Convenient ports with removable covers allow cable routing through top

Highlights

- Maximum load capacity of 250 lbs (113.4 kgs)
- Swings away from wall bracket on a hinge for easy access
- Locking steel cabinet vented at sides, top and bottom
- Secures 12U of 19 in. rack equipment up to 32.5 in. deep
- Mounts to wall or rolls on floor (with optional SRCASTER)

Package Includes

- SRW12US33G SmartRack 12U Server-Depth Wall-Mount Rack Enclosure Cabinet
- (36) M6 screws
- (36) M6 cage nuts
- (36) M6 washers
- (36) 12-24 screws
- (2) Keys
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

and bottom

Easy Enclosure and Equipment Installation Vertical mounting rails adjust in 7/8 in. increments to house equipment up to 32.5 in. deep Ships fully assembled for quick installation Mounts to wall or rolls on floor with optional SRCASTER caster kit Wall-mounting holes spaced 16 in. apart to accommodate standard wall stud placement Rails support square-hole or 12-24 threaded-hole mounting Rack spaces numbered for easy reference

Meets Payment Card Industry Standards Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

OVERVIEW	
UPC Code	037332187352
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Small Enclosure
PHYSICAL	
Color	Black
Rack Height	12U
Rack Depth	Mid
Factory Preset Rack Depth (in.)	25.99
Factory Preset Rack Depth (cm)	66.0
Factory Preset Rack Depth (mm)	660
Maximum Device Depth (cm)	82.55
Maximum Device Depth (in.)	32.5
Maximum Device Depth (mm)	826
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Shipping Dimensions (hwd / in.)	30.20 x 26.10 x 36.06
Shipping Dimensions (hwd / cm)	76.71 x 66.29 x 91.59
Shipping Weight (lbs.)	118.00
Shipping Weight (kg)	53.52
Unit Dimensions (hwd / in.)	25.100 x 23.600 x 33.500
Unit Dimensions (hwd / cm)	63.5 x 60 x 85.09
Unit Weight (lbs.)	94.5
Unit Weight (kg)	42.86



Powering Business Worldwide

TRIPP LITE
SERIES

Weight Capacity - Stationary (kg)	113
Weight Capacity - Stationary (lbs.)	250
Number of Vertical Mounting Rails	4
FEATURES & SPECIFICATIONS	
Grounding Details	Front and Back door frames
Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.