
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT – By – ALL RIGHTS RESERVED.


| | |
|---|---|
| PROJECT | PRJ–16–000909157 |
| PART NO. | X–2308330–X |
| DESCRIPTION | FULL METAL HOODS SIZE 4 |
| CUSTOMER | GENERAL MARKET |

| REVISIONS | | | | | |
|---|---|---|---|---|---|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | A2 | REVISED PER ECR–16–014891 | 20OCT2016 | KK | GG |

## X–2308330–X






CRIMP FLANGE




CRIMP BARREL





CABLE CLAMP

HOUSING 1





HOUSING 2



BLIND PLATE



CABLE BUSHING

NOTES:

1. TEMPERATURE: –40°C TO +90°C.
2. STRAND DIAMETER OF CRIMP FLANGE: 2.7–8.7 mm.
3. CABLE DIAMETER WITH EXTERNAL CABLE CLAMP: 4–14 mm.
4. CABLE DIAMETER WITH INTERNAL CABLE CLAMP: d=4–11mm (FOR d=4–7 mm TURN CABLE CLAMP).
5. CABLE BUSHING FOR CABLE DIAMETER 4–9 mm.

* CRIMP FLANGE PN *–2308349–* TO BE ORDERED SEPARATELY.
* CRIMP BARREL TO BE USED IN COMBINATION WITH THE FLANGE PN *–2308350–* TO BE ORDERED SEPARATELY.
* CABLE CLAMP SCREW VERSION PN *–2308272–* TO BE ORDERED SEPARATELY.

| ASSY. PART NO. | DESCRIPTION | SUB–PART DESCRIPTION POS.1 | POS. 3 | POS. 5 | POS. 6 | POS. 7 | WEIGHT, g |
|---|---|---|---|---|---|---|---|
| 1–2308330–5 | FULL METAL HOOD4 5 | HOUSING 2 | 1 | 2 | 2 | 3 | 92 |
| 1–2308330–4 | FULL METAL HOOD4 4 | HOUSING 2 | 2 | 1 | 1 | 2 | 94 |
| 1–2308330–3 | FULL METAL HOOD4 3 | HOUSING 2 | 1 | 2 | – | 3 | 90 |
| 1–2308330–2 | FULL METAL HOOD4 2 | HOUSING 2 | 2 | 1 | – | 2 | 92 |
| 1–2308330–1 | FULL METAL HOOD4 1 | HOUSING 1 | 2 | – | – | – | 87 |

| SL NO. | QTY | ASSY. PART NO. | DESCRIPTION (MATERIAL, FINISH) |
|---|---|---|---|
| 9 | 1 | – | SCREW M2.5x5 (CASE HARDENING STEEL, ZINC–PLATED) |
| 8 | 4 | – | SCREW M2.5x6.5 (CASE HARDENING STEEL, ZINC–PLATED) |
| 7 | SEE TAB. POS.7 | – | SCREW M2.5x6 (CASE HARDENING STEEL, ZINC–PLATED) |
| 6 | SEE TAB. POS.6 | – | CABLE BUSHING (EPTR SANTOPRENE) |
| 5 | SEE TAB. POS.5 | – | CABLE CLAMP (BAND STEEL, ZINC–PLATED) |
| 4 | 2 | – | CATCH SPRING (STAINLESS STEEL, RAW) |
| 3 | SEE TAB. POS.3 | – | BLIND PLATE (ZINC ALLOY, RAW) |
| 2 | 1 | – | COVER (ZINC ALLOY, RAW) |
| 1 | 1 | SEE TAB. POS.1 | HOUSING (ZINC ALLOY, RAW) |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN ISO 2768 m

| | |
|---|---|
| 0 PLC | ± – |
| 1 PLC | ± – |
| 2 PLC | ± – |
| 3 PLC | ± – |
| 4 PLC | ± – |
| ANGLES | ± – |

MATERIAL: –

FINISH: –

| | | |
|---|---|---|
| DWN | KIRAN K | 02AUG2016 |
| CHK | GUNASEKHAR G | 02AUG2016 |
| APVD | GUNASEKHAR G | 02AUG2016 |
| PRODUCT SPEC | – | |
| APPLICATION SPEC | – | |
| WEIGHT | | |

TE Connectivity

NAME: FULL METAL HOODS SIZE 4

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A2 | 00779 | C–2308330 | – |

CUSTOMER DRAWING | SCALE NTS | SHEET 1 OF 1 | REV A2

2308330



Downloaded from Arrow.com.