

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0530151510

Status:


Active

Overview:

MicroBlade™ Connection System

Description:

2.00mm Pitch MicroBlade™ Wire-to-Board Header, Right Angle, 15 Circuits



Documents:	
3D Model	Product Specification PS-51004-002-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	53015
Application	Signal, Wire-to-Board
Overview	MicroBlade™ Connection System
Product Name	MicroBlade™
UPC	800753750890
Physical	
Breakaway	No
Circuits (Loaded)	15
Circuits (maximum)	15
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1308.900/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.50mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-20°C to +85°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	125V
Material Info	

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per

-ED/01/2017 (12

January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

53015 Series

Mates With

51004 Crimp Housing, 50011 Crimp

Terminal

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-51004-002-001
SD-53015-**10

This document was generated on 07/26/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION