

Online Catalog

Welcome to Laird Technologies' Online Catalog.



HOME > ONLINE CATALOG

Antennas & Reception Solutions

Vehicular Antennas & Telematics
Base Station & Backhaul Antennas
In-Building, CPE, Access Point, &
Mobile Client Antennas
RFID Antennas
Mobile Radio Antennas

EMI Solutions

EMI Shielding & Gaskets
Specialty EMI Solutions
Ferrite Products

Thermal Management Solutions

Thermal Interface Materials
Thermally Conductive PCB Materials
Thermoelectric Assemblies
Thermoelectric Modules

Wireless Solutions & M2M

Telematics & Tracking Devices
Proprietary Radio Modules
ZigBee Radio Modules
Bluetooth Radio Modules
WLAN Radio Modules

Search Catalog

SEARCH

[All Categories](#) > [EMI Solutions](#) > [EMI Shielding & Gaskets](#) > [Fingerstock and Spring Contacts](#) > [Fingerstock, Gaskets & Metal Grounding Products](#) > [Fingerstock Gaskets and Metal Grounding Products](#) > [Gasket](#) > [Strip Metal Gaskets](#) > [UltraFlex D with PSA Copper Knitted Wire Shielding](#) > [Item # 8102-0205-40](#)


Request Information

Item # 8102-0205-40, UltraFlex D with PSA Copper Knitted Wire Shielding


Stock Locator

UltraFlex ElectroNit combines the optimum mechanical properties of beryllium copper with shielding effectiveness as much as 20 dB higher than conventional materials. It offers superb resiliency for consistent, point-to-point contact requiring the lowest compression forces among all other shielding materials and configurations. A wide range of platings, sizes, configurations, and excellent flexibility create optimum design latitude.

- Other platings available upon request



[larger image](#)



[larger image](#)

- [Download PDF](#)
- [Printable Page](#)
- [Email This Page](#)
- [Save To Favorites](#)

MORE IMAGES

- [O Ring Construction](#)
- [Cut to Length](#)
- [Compression Deflection Curve](#)
- [Shielding Effectiveness](#)
- [Dimensional Drawing - Ultraflex D with PSA](#)

Specifications	Features	Compression Recovery	Fabricated UltraFlex Gaskets
Width	0.380 inches		
Width	9.7 mm		
Height	0.312 inches		
Height	7.9 mm		
Width Tolerance	0.040 inches		
Width Tolerance	1 mm		
Height Tolerance	0.040 inches		
Height Tolerance	1 mm		
Plating Options	Cadmium Plate Nickel Plate Tin Plate Zinc Clear Chromate		

Request Information