

CHERRY MC 1000



Models may vary from the image shown

Simple business mouse in CHERRY quality

CHERRY MC 1000 offers the best quality in its price class. The focus is on durability and on reliable and precise working - whether for use privately or in professional office workstations.

Key benefits

- 3-button mouse with scroll wheel
- Resolution 1,200 dpi
- GS certification
- Suitable for both right-handed and left-handed operation
- Symmetrical design
- Standard size

Technical Data:

Weight (product):

90 g

Total weight (with packaging):

128 g

Cable Length:

approx. 1.80 m

Storage Temperature:

-15°C to 60°C

Operating Temperature:

0°C to 40°C

Current Consumption:

max. 50 mA

Interface:

- USB

Product approvals:

- c-tick
- UL
- CE
- FCC
- TÜV-Süd/GS



System requirements:

- USB connection

Delivery Volume:

- CHERRY MC 1000
- Operating instructions in hard copy

Dimensions (product):

109 x 62 x 37 mm

Packaging dimensions:

130 x 100 x 43 mm

Reliability:

- Standard keys: >3 mill. operations
- MTBF > 45,000 hours

Mouse:

- Scanning: Optical
- Resolution: 1200 dpi
- Number of Keys: 3
- Mouse wheel design: Scroll wheel with key function
- Design: Symmetrical
- Connection: USB
- Housing colour: black
- Key colour: Product dependant, see table "Models"

Packaging Unit:

- Number of products in the master package: 10
- Number of master packages per pallet: 125

Warranty:

3-year limited manufacturer's guarantee

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty:

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase. CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in

particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Mouse Key colour
1	CHERRY MC 1000	JM-0800-0	4025112083358	pale grey
2	CHERRY MC 1000	JM-0800-2	4025112083341	black